



IQ COLOR has the invaluable ability to magnetically draw attention. The expressive paper emphasises your sophisticated and unique appearance. With its 36 colours, it creates vibrant possibilities to present your ideas emphatically in pale pastels and colour-intense shades, with cheery neons and even with elegant black. IQ COLOR is all about flexibility and, with its flawless environmental profile is simply impressive. A paper, that shines in all shades.



Technical Data: IQ COLOR

Basis weight	g/m ²	ISO 536	120 ± 4.0
Caliper	µm	ISO 534	159 ± 6
Roughness Bendtsen	ml/min	ISO 8791-2	230 ± 50
Moisture abs.	%	ISO 287	4.8 ± .5

Product meets EN 12281, requirements for copy paper for dry toner imaging processes and ISO 20494, requirements for permanence for paper. Production processes certified according to ISO 9001, ISO 45001 and OHSAS 18001. Standard measurement uncertainty between laboratories is not incorporated.

SIGNIFICANCE OF VALUES: 2 SIGMA

This specification is valid for one year after issue or good till cancelled.