

TEKNISK SPECIFIKATION TECHNICAL SPECIFICATION TECHNISCHE SPECIFIKATION		MASCOT WORKWEAR	
Kvalitet/ Quality/ Qualität: 194	Dato/ Date/ Datum: 27.01.2010		
			Standard/ Method/ Standard
Vægt/ Weight/ Gewicht	g/m ²	270	EN 12127
Komposition/ Composition/ Gwebemischung	%	100 Pes +PU coating	
Konstruktion/ Construction/ Webkonstruktion	2/2 Panama (canvas)		
STYRKE /PHYSICAL PROPERTIES/ FESTIGKEIT			
Slidstyrke/ Abrasion resistance/ Strapazierfähigkeit (Mindestwert)	t	>150.000	EN ISO 12947
Brudstyrke kæde/ Tensile Warp/ Bruchfestigkeit Kette (Mindestwert)	N.	-	EN ISO 13934-1
Brudstyrke skud/ Tensile Weft Bruchfestigkeit Schuss (Mindestwert)	N.	-	EN ISO 13934-1
Rivstyrke kæde/ Tearing strength Warp/ Reißfestigkeit Kette (Mindestwert)	N.	-	ISO 13937-2
Rivstyrke skud/ Tearing strength Weft/ Reißfestigkeit Schuss (Mindestwert)	N.	-	ISO 13937-2
FARVEÆGTHEDER/ COLOUR FASTNESS/ FARBECHTHEIT			
Vask/ Washing/ Waschepochtheit	Note	4-5	ISO 105-C06
Sved/ Perspiration/ Schweißepochtheit	Note	4-5	ISO 105-E04
Lys/ light/ Lichtepochtheit	Note	-	ISO 105-B04
Gnid, våd/ Rubbing, wet/ Reibepochtheit nass (Kette/Schuss)	Note	4	ISO 105-X12
Gnid, tør/ Rubbing dry/ Reibepochtheit trocken (Kette/Schuss)	Note	4	ISO 105-X12
Dimensionsstabilitet/ Dimensional stability/ Dimensionsstabilität	%	+/-1%	ISO 25077
Vandsøjle/ Water resistance/ Wassersäule	mm H ₂ O	10.000	ISO 20811
Åndbarhed/ Water vapour permeability/ Atmungsaktivitât		EN343 class 3	CUP METHOD
Finish/ Finish/ Ausführung			
Vaskesymboler/Landry symbols/ Pflegesymbole	 Undgå skyllemiddel/Do not use softner/kein Weichspûlmittel brauchen Må ikke industrivaskes/ Do not industrial wash/ Keine industriewäsche		