




LV HRC FUSE BASE 690V(1000V) SINGLE-POLE, 160A, SIZE 00 STRAIGHT-WIRE TERMI.2.2-50SQMM

Model		
product brand name		SENTRON
Design of the product		LV HRC fuse base
General technical data		
Number of poles		1
Size of fuse system / acc. to DIN EN 60269-1		Other
Usage category		Without
circuit-breaker / Design		3NH30
Electricity		
rated current I <sub>n</sub> / IEC, DIN/VDE / at 40 Cel	A	147.2
Current / with AC / Rated value	A	160
Product details		
Product component / Swivel mechanism		No
Connections		
Tightening torque / with screw-type terminals / maximum	N·m	14
Type of electrical connection		with plug-in terminal
• for main current circuit		tab connection
Mechanical Design		
Height	mm	128
Depth	mm	60
Mounting type		fixed mounting
Mounting type / bus-mounting		No

General Product Approval				Declaration of Conformity	Test Certificates
 CSA	 KEMA	 GOST		 EG-Konf.	<a href="#">Type Test Certificates/Test Report</a>

Shipping Approval	other
 GL	<a href="#">Environmental Confirmations</a>

#### Further information

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://eb.automation.siemens.com/mall/en/WW/Catalog/Product/3NH3031>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<http://support.automation.siemens.com/WW/view/en/3NH3031/all>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mfb=3NH3031](http://www.automation.siemens.com/bilddb/cax_en.aspx?mfb=3NH3031)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://ausschreibungstexte.siemens.com/tiplv>

last modified:

11.03.2015