



Halogen non-reflector

7158 150W G6.35 24V 1CT/10X10F

Halogen non-reflector lamps offer high-quality light and are easy to install, replace and operate. All halogen non-reflector lamps incorporate a distortion-free quartz bulb and a precise positioning of the mounted filament. These ensure optimal beam performance and consistent, high light output. A wide range of wattages is available for a broad variety of applications, including projection systems. In addition you get all the proven advantages of halogen technology such as a full spectrum and a color rendering index (CRI) of 100 – the same as natural light and the best that it can be. Halogen lamps also create a comfortable warm white light, and they maintain their lumen output, with almost no reduction, throughout their lifetime.

Product data

General information						
Cap-Base	G6.35 [G6.35]					
Philips Code	7158					
ANSI Code	FCS					
LIF Code	A1/216					
Operating Position	S90 [Standing +/-90D or Base Down					
	(BDH)]					
Main Application	Projection					
Life to 50% Failures (Nom)	50 h					
Light technical						
Luminous Flux (Rated) (Nom)	5200 lm					
Correlated Color Temperature (Nom)	3450 K					
Color Rendering Index (Nom)	100					
Operating and electrical						
Power (Nom)	150 W					

Voltage (Nom)	24 V				
Mechanical and housing					
Bulb Material	terial Quartz-UV Open				
Filament Shape	Flat				
Filament Dimensions WxH	5.8x2.9				
Luminaire design requirements					
Bulb Temperature (Max)	nperature (Max) 900 °C				
Pinch Temperature (Max)	400 °C				
Pinch Temperature (Max)-DUP(do not use) 400 °C					
Product data					
Full product code	871150040983650				
Order product name	7158 150W G6.35 24V 1CT/10X10F				
EAN/UPC - Product	8711500409836				
Order code	923870520503				
Numerator - Quantity Per Pack	1				


Datasheet, 2022, September 12 data subject to change

Halogen non-reflector

Local code description	7158 150W G6.35 24V 1CT/10X10F				
Numerator - Packs per outer box	100				
Material Nr. (12NC)	923870520503				

Net Weight (Piece)	0.004 kg	
--------------------	----------	--

Dimensional drawing



7158 150W G6.35 24V 1CT/10X10F

Product	D (max)	L (min)	L (max)	L	P (max)	Р	P (min)	C (max)
7158 150W	11.5 mm	31.5 mm	32.25	32	1.05 mm	1 mm	0.95	50 mm
G6.35 24V			mm	mm			mm	
1CT/10X10F								

