



10.1" Diagonal - 1280x800 IPS HDMI/VGA/AV Display

SKU:FIT0476

INTRODUCTION

This 10.1 inch high-resolution 1280*800 IPS display is especially designed as a monitor for LattePanda(which could be used as windows 10 development board), Raspberry Pi and other mini PC. The HDMI/VGA/AV interfaces ensure its wide compatibility. Making a digital photo frame, playing a video, adding a face for your robot, you can expand your imagination, make more fun.



Note: A 7.5~12V DC power adapter is needed for this monitor. Click [Wall Adapter Power Supply](#) to get it.
V1.1 increase an audio port.

SPECIFICATION

- Screen size: 10.1 inch
- Screen Dimensions: 217 * 135mm/ 8.54 * 5.31 inches (16:10)
- Display Dimensions: 230 * 149 * 5.0mm/9.05 * 5.86 * 0.2 inches
- Panel Type: a-Si TFT-LCD Panel
- Resolution (RGB): 1280x800, WXGA
- Display Mode: HFFS, Normally Black, Transmissive
- Surface: Hard coating
- Brightness: 350 cd/m²
- Contrast Ratio: 800:1 (Min.)
- Input Voltage: 7.5~12V
- Rated power: 6-7.5W
- Signal input: AV + VGA + HDMI (HDMI 1.2)
- Support Audio Output
- Weight: 358g

SHIPPING LIST

- HDMI+VGA+2AV LCD controller board x1
- 10.1 inch 1280x800 IPS LCD panel x1
- Spaker (Pair) x1
- LVDS Cable x1
- Keyboard with Wire x1

