

CNC precision short drill chuck

In accordance with ISO 7388-1 (DIN 69871)

ALBRECHT
Präzisionsspannhalter

Application:

For use on machining centres and CNC machines with tool change systems. For drilling, reaming, countersinking and also light milling and finishing tasks.

Execution:

- 100 % concentricity check using different test pin diameters at various measuring points, based on DIN ISO 10888.
- Concentricity tolerance ≤ 0.03 mm across the entire clamping range.
- With worm gear.
- Relevant parts hardened and ground.

Advantage:

- Accident-proof as opening of the chuck during operation or on a sudden spindle stop is not possible.
- Integrated worm gear ensures high retention torque < 75 Nm with 13 mm diameter.

Delivery:

1x CNC precision short drill chuck in accordance with ISO 7388-1 (DIN 69871); incl. hexagon key.



Art. no.	23050 545
Brand	ALBRECHT
Manufacturer Part Number	800 116Z 240 0
Tool holding device	SK 40
Min./max. clamping width	1-16 mm
Projecting length	80 mm
Outer diameter	50 mm
Length closed	92 mm
Concentricity tolerance	0.03 mm
Coolant supply	Internal axial
Balancing quality	G 2.5 at 20 rpm
Gross Weight	1.589 kg
Product Group	209

EAN

4250261589448