

## Electronic torque tester DremoTest E

With calibration certificate



### Application:


For checking and adjusting all clockwise torque wrenches used in workshops, in industry and for quality assurance processes.

### Execution:

- With auto-reset function
- 1st peak value recognition (first peak/crunch point recognition)
- Fixed hexagonal box nut mount
- Convertible between Nm and lbf.ft, integrated measuring transducer
- Serial RS232 interface

### Advantage:

- Simple to use and with a robust design



<b>Art. no.</b>	<b>52292 650</b>
<b>Brand</b>	GEDORE
<b>Manufacturer Part Number</b>	1947702
<b>Min. torque</b>	90 Nm
<b>Max. torque</b>	1100 Nm
<b>Drive</b>	1/2 inch, 3/4 inch
<b>Min./max. torque</b>	90-1100 Nm
<b>Error limit (%)</b>	1 %
<b>Calibration certificate</b>	Yes
<b>Gross Weight</b>	11.916 kg
<b>Product Group</b>	556

### EAN

4002805929148