

# Crimping pliers for industrial use PV-CZM...

Only the tools stated below shall be used for the assembly of UL- and TÜV Rheinland approved products.

These are suited for the processing of high numbers of pieces and can be adjusted to

the product with the help of changeable locators and crimp inserts.

PV-CZM...



Order No.	Type	Designation	Crimp range		MA	Assembly instruction
			mm <sup>2</sup>	AWG		
32.6020-40100	PV-CZM-40100	Crimping pliers incl. locator and insert	2.5; 4	16; 14; 12	MA251	
32.6020-41100	PV-CZM-41100		2.5; 4; 6	14; 12; 10		
32.6020-42100	PV-CZM-42100		4; 10	12; 8		

### Individual parts


32.6021-40100	PV-ES-CZM-40100	Insert	2.5; 4	16; 14; 12	MA251
32.6021-41100	PV-ES-CZM-41100	Insert	2.5; 4; 6	14; 12; 10	MA251
32.6021-42100	PV-ES-CZM-42100	Insert	4; 10	12; 8	MA251
32.6056	PV-LOC-C	Locator	all sizes		MA251

## Tools

### Open-end spanner sets

To tighten and unscrew the cable gland and to open the locking device of the connection.

PV-MS



PV-MS-PLS



Order No.	Type	Designation	MA	Assembly instruction
32.6024	PV-MS	Open-end spanner set (2 pcs.), plastic	MA298, MA299	
32.6058	PV-MS-PLS	Open-end spanner set (2 pcs.), metal	MA298, MA299	