

# HPCR0819AK1K0ST ✓ ACTIVE

CGS | CGS HPCR

TE Internal #: 2-2176471-8

Through-Hole Resistors, Power Resistor, 19.1 x 7.9 mm, 2


Termination, Reel/Box, 10 %, Ceramic Composition, Resistance

Class 1kΩ – 1MΩ, CGS HPCR

[View on TE.com >](#)



Passive Components > Resistors > Through-Hole Resistors



Resistor Type: **Power Resistor**

Passive Component Dimensions: **19.1 x 7.9 mm**

Number of Terminations: **2**

Packaging Method: **Reel/Box**

Passive Component Tolerance: **10 %**

## Features

### Product Type Features

|               |                     |
|---------------|---------------------|
| Product Type  | Fixed Resistor      |
| Resistor Type | Power Resistor      |
| Element Type  | Ceramic Composition |

### Configuration Features

|                     |   |
|---------------------|---|
| Number of Resistors | 1 |
|---------------------|---|

### Electrical Characteristics

|                             |           |
|-----------------------------|-----------|
| Passive Component Tolerance | 10 %      |
| Resistance Class            | 1kΩ – 1MΩ |
| Resistance Value            | 1.0K Ω    |
| Power Rating                | 2 W       |

### Body Features

|                             |              |
|-----------------------------|--------------|
| Passive Component Lead Type | Axial-Leaded |
|-----------------------------|--------------|

### Termination Features

|  |  |
|--|--|
|  |  |
|--|--|



|                                             |                     |
|---------------------------------------------|---------------------|
| Number of Terminations                      | 2                   |
| Passive Component Termination Material Type | Tinned Copper Leads |

### Dimensions

|                              |               |
|------------------------------|---------------|
| Passive Component Dimensions | 19.1 x 7.9 mm |
|------------------------------|---------------|

### Usage Conditions

|                         |                  |
|-------------------------|------------------|
| Temperature Coefficient | +0 / -800 ppm/°C |
|-------------------------|------------------|

### Packaging Features

|                  |          |
|------------------|----------|
| Packaging Method | Reel/Box |
|------------------|----------|

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

|                                               |                                                                                                                                         |
|-----------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                                                                                                               |
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                                                               |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                                 |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JAN 2022 (223)<br>Candidate List Declared Against: JUL 2021 (219)<br>SVHC > Threshold:<br>Not Yet Reviewed |
| Halogen Content                               | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free                                                     |
| Solder Process Capability                     | Wave solder capable to 265°C                                                                                                            |

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



## Also in the Series | CGS HPCR



### Documents

#### Product Drawings

[HPCR 0819 A 10% 1K0 Std T&R](#)

English

#### CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_2-2176471-8\\_A.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_2-2176471-8\\_A.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_2-2176471-8\\_A.3d\\_stp.zip](#)

English

HPCR0819AK1K0ST

Through-Hole Resistors, Power Resistor, 19.1 x 7.9 mm, 2 Termination, Reel/Box, 10 %, Ceramic Composition, Resistance Class 1k $\Omega$  – 1M $\Omega$ , CGS HPCR



By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

## Datasheets & Catalog Pages

### Bulk Ceramic Resistors - Type HPCR Series - Tyco Electronics Passives

English