

Reversible ratchet HIPER extra long 90 T 415 mm

1/2" square drive 12.5, DIN 3120



Application:

Strict manufacturing tolerances guarantee protection against invasive contamination

Execution:

- Load capacity of up to 1000 Nm
- Ball lock, 2-C handle
- Reversing lever with locking function offers protection against unwanted reversing
- Finely toothed, 90 teeth, 4° actuation angle

Advantage:

- Extremely high performance compared to ratchets with similar dimensions



Art. no.	58890 110
Brand	HAZET
Manufacturer Part Number	916HPL
Tip size	1/2 inch
Length	415 mm
Number of teeth	90 PCS
Returning angle	4 Degree
Surface	Chrome plated
Material	Chrome-vanadium steel
Material of handle	2-component plastic
Gross Weight	0.907 kg
Product Group	569

EAN

4000896219209