

forum Passungstabelle für 1/100 Maschinenreibahlen ähnlich DIN 212

Bohrungs- Ø in mm	C 8	C 9	C 10	C 11	CD 7	D 7	D 8	D 9	D 10	D 11	D 12	E 7	E 8	E 9	EF 8	F 7	F 8	F 9
1,0	1,07	1,07	1,08	1,10	1,04	1,02	1,03	–	1,04	1,06	1,08	1,02	1,02	1,03	1,02	1,01	1,01	1,02
2,0	2,07	2,07	2,08	2,10	2,04	2,04	2,03	–	2,04	2,06	2,08	2,02	2,02	2,03	2,02	2,01	2,01	2,02
3,0	3,07	3,07	3,08	3,10	3,04	3,04	3,03	–	3,04	3,06	3,08	3,02	3,02	3,03	3,02	3,01	3,01	3,02
4,0	4,08	4,09	–	–	4,05	4,04	4,04	4,05	4,06	4,08	4,10	–	4,03	4,04	4,03	–	4,02	4,03
5,0	5,08	5,09	–	–	5,05	5,04	5,04	5,05	5,06	5,08	5,10	–	5,03	5,04	5,03	–	5,02	5,03
6,0	6,08	6,09	–	–	6,05	6,04	6,04	6,05	6,06	6,08	6,10	–	6,03	6,04	6,03	–	6,02	6,03
7,0	7,09	7,10	–	–	7,06	7,05	7,05	7,06	7,08	7,10	–	7,03	7,04	7,05	7,03	7,02	7,03	–
8,0	8,09	8,10	–	–	8,06	8,05	8,05	8,06	8,08	8,10	–	8,03	8,04	8,05	8,03	8,02	8,03	–
9,0	9,09	9,10	–	–	9,06	9,05	9,05	9,06	9,08	9,10	–	9,03	9,04	9,05	9,03	9,02	9,03	–
10,0	10,09	10,10	–	–	10,06	10,05	10,05	10,06	10,08	10,10	–	10,03	10,04	10,05	10,03	10,02	10,03	–
11,0	–	–	–	–	–	11,06	–	11,08	11,10	–	–	11,04	11,05	11,06	–	–	11,03	11,04
12,0	–	–	–	–	–	12,06	–	12,08	12,10	–	–	12,04	12,05	12,06	–	–	12,03	12,04

Bohrungs- Ø in mm	F 10	G 6	G 7	H 5	H 6	H 7	H 8	H 9	H 10	H 11	H 12	H 13	J 6	J 7	J 8	JS 7	JS 8	JS 9
1,0	–	–	1,01	1,00	1,00	–	1,01	–	1,02	1,04	1,06	1,09	1,00	1,00	1,00	1,00	1,00	1,00
2,0	–	–	2,01	2,00	2,00	–	2,01	–	2,02	2,04	2,06	2,09	2,00	2,00	2,00	2,00	2,00	2,00
3,0	–	–	3,01	3,00	3,00	–	3,01	–	3,02	3,04	3,06	3,09	3,00	3,00	3,00	3,00	3,00	3,00
4,0	4,04	4,01	4,01	4,00	4,00	–	4,01	4,02	4,03	4,05	4,08	–	4,00	4,00	4,00	4,00	4,00	4,00
5,0	5,04	5,01	5,01	5,00	5,00	–	5,01	5,02	5,03	5,05	5,08	–	5,00	5,00	5,00	5,00	5,00	5,00
6,0	6,04	6,01	6,01	6,00	6,00	–	6,01	6,02	6,03	6,05	6,08	–	6,00	6,00	6,00	6,00	6,00	6,00
7,0	7,05	7,01	7,01	7,00	7,00	7,01	7,01	7,02	7,04	7,06	7,10	–	7,00	7,00	7,00	7,00	7,00	–
8,0	8,05	8,01	8,01	8,00	8,00	8,01	8,01	8,02	8,04	8,06	8,10	–	8,00	8,00	8,00	8,00	8,00	–
9,0	9,05	9,01	9,01	9,00	9,00	9,01	9,01	9,02	9,04	9,06	9,10	–	9,00	9,00	9,00	9,00	9,00	–
10,0	10,05	10,01	10,01	10,00	10,00	10,01	10,01	10,02	10,04	10,06	10,10	–	10,00	10,00	10,00	10,00	10,00	–
11,0	11,06	10,01	–	11,00	–	11,01	11,02	11,03	11,05	11,07	–	–	11,00	11,00	11,00	11,00	11,00	–
12,0	12,06	12,01	–	12,00	–	12,01	12,02	12,03	12,05	12,07	–	–	12,00	12,00	12,00	12,00	12,00	–

Bohrungs- Ø in mm	K 6	K 7	K 8	M 6	M 7	M 8	N 6	N 7	N 8	P 6	P 7	P 8	R 6	R 7	S 6	S 7	U 6	U 7
1,0	–	–	0,99	–	–	0,99	0,99	0,99	0,99	0,99	0,99	0,99	–	–	0,98	0,98	0,98	0,98
2,0	–	–	1,99	–	–	1,99	1,99	1,99	1,99	1,99	1,99	1,99	–	–	1,98	1,98	1,98	1,98
3,0	–	–	2,99	–	–	2,99	2,99	2,99	2,99	2,99	2,99	2,99	–	–	2,98	2,98	2,98	2,98
4,0	4,00	4,00	4,00	3,99	–	3,99	3,99	3,99	3,99	–	–	3,98	–	–	3,98	3,98	–	–
5,0	5,00	5,00	5,00	4,99	–	4,99	4,99	4,99	4,99	–	–	4,98	–	–	4,98	4,98	–	–
6,0	6,00	6,00	6,00	5,99	–	5,99	5,99	5,99	5,99	–	–	5,98	–	–	5,98	5,98	–	–
7,0	–	7,00	7,00	6,99	6,99	6,99	–	6,99	6,99	–	–	–	6,98	6,98	–	–	6,97	6,97
8,0	–	8,00	8,00	7,99	7,99	7,99	–	7,99	7,99	–	–	–	7,98	7,98	–	–	7,97	7,97
9,0	–	9,00	9,00	8,99	8,99	8,99	–	8,99	8,99	–	–	–	8,98	8,98	–	–	8,97	8,97
10,0	–	10,00	10,00	9,99	9,99	9,99	–	9,99	9,99	–	–	–	9,98	9,98	–	–	9,97	9,97
11,0	–	11,00	11,00	10,99	10,99	10,99	–	10,99	10,99	10,98	10,98	10,97	–	–	10,97	10,97	–	–
12,0	–	12,00	12,00	11,99	11,99	11,99	–	11,99	11,99	11,98	11,98	11,97	–	–	11,97	11,97	–	–

Bohrungs- Ø in mm	X 7	X 8	X 9	Z 7	Z 8	Z 9	Z 10	ZA 7	ZA 8	ZA 9	ZB 8	ZB 9
1,0	–	0,97	0,97	0,97	0,97	–	0,96	0,96	–	–	0,95	0,95
2,0	–	1,97	1,97	1,97	1,97	–	1,96	1,96	–	–	1,95	1,95
3,0	–	2,97	2,97	2,97	2,97	–	2,96	2,96	–	–	2,95	2,95
4,0	3,97	–	3,96	3,96	3,96	3,95	3,95	3,96	–	–	3,94	3,94
5,0	4,97	–	4,96	4,96	4,96	4,95	4,95	4,96	–	–	4,94	4,94
6,0	5,97	–	5,96	5,96	5,96	5,95	5,95	5,96	–	–	5,94	5,94
7,0	–	6,96	6,95	6,96	6,95	–	6,94	6,94	6,94	–	–	6,92
8,0	–	7,96	7,95	7,96	7,95	–	7,94	7,94	7,94	–	–	7,92
9,0	–	8,96	8,95	8,96	8,95	–	8,94	8,94	8,94	–	–	8,92
10,0	–	9,96	9,95	9,96	9,95	–	9,94	9,94	9,94	–	–	9,92
11,0	10,96	10,95	–	10,95	10,94	–	10,93	–	10,93	–	10,90	10,90
12,0	11,96	11,95	–	11,95	11,94	–	11,93	–	11,93	–	11,90	11,90

