

Handheld Megohmmeter

1000V digital tester
With large dual backlit display

Features:

- Double molded housing for added durability
- Dual display of Insulation Resistance and Test Voltage
- Backlit super large display
- 250V, 500V, and 1000V test voltages
- Insulation Resistance to 2000M Ω
- Auto power off
- Lo Ω function for testing connections
- Lock Power On Function for hands-free operation
- Data Hold to freeze displayed reading
- Complete with heavy duty test leads, alligator clip test lead, hanging strap, hard carrying case, and 6 x AA batteries



Specifications	
Insulation Resistance	200M Ω , 2000M Ω
Max Resolution	0.1M Ω
Basic Accuracy	$\pm 3\%$
Insulation Test Voltages	250V, 500V, 1000V
AC Voltage Test	Yes
Low Resistance Test	Yes
Power source	6 x AA batteries
Dimensions	7.8 x 3.6 x 1.9" (200 x 92 x 50mm)
Weight	24.6oz (700g)

Ordering Information:

- 380260.....Handheld Megohmmeter
 380260-NIST380260 with Calibration Traceable to NIST
 TL805.....Double Injected Test Leads

