


E11440



Jumper cable with valve plug

VVSAC031MSS0005H03STGH030MSS




| Application | | |
|--|--|-----------------|
| Special feature | Free from silicone; Halogen-free; Gold-plated contacts | |
| Free from silicone | yes | |
| Electrical data | | |
| Operating voltage [V] | < 24 AC/DC | |
| Overtoltage protection | yes; (VDR) | |
| Max. current load total [A] | 3 | |
| Operating conditions | | |
| Ambient temperature [°C] | -25...80 | |
| Protection | IP 67 | |
| Mechanical data | | |
| Weight [g] | 263.2 | |
| Materials | PUR | |
| Material nut | brass, nickel-plated / brass, nickel-plated | |
| Displays / operating elements | | |
| Display | switching status | 1 x LED, yellow |
| Accessories | | |
| Accessories (supplied) | screw panel for labelling | |
| Remarks | | |
| Pack quantity | 1 pcs. | |
| Electrical connection - plug | | |
| Connector: 1 x M12, straight; Moulded body: PUR; Locking: brass, nickel-plated; Contacts: gold-plated; Tightening torque: 0.7...0.9 Nm | | |

E11440



Jumper cable with valve plug


VVSAC031MSS0005H03STGH030MSS



Electrical connection

Cable: 5 m, PUR, Halogen-free, black, Ø 5 mm; 3 x 0.5 mm² (42 x Ø 0.1 mm)

Connection



Electrical connection - socket

Connector: 1 x valve type C industrial standard, angled; Moulded body: PUR; Locking: brass, nickel-plated; Contacts: nickel-plated brass; Tightening torque: 0.7...0.9 Nm

