Cliff Electronic Components Ltd.

76 Holmethorpe Avenue, Holmethorpe Industrial Estate, Redhill, Surrey, RH1 2PF, England, UK

Tel: 01737-771375 Fax: 01737-766012 Website: www.cliffuk.co.uk

PART NUMBER: OD6634 BEVEL CUT NIPPERS BS/3058

Pliers and nippers - General technical requirements

Handgrip

The handle are shaped to have a comfortable and firm grip; they are in plastic.

Hinge

The hinge is made to open and close the tool easily; it has not an excessive lateral play that could damage the functional of the tool.

Beaks

The beaks of the nipper can join together.

The hardness of the steel is 55 HRC.


Finishing of the tool

The tools are without flash or sharp border so it can be used with safety; they are subject to a treatment of burnishing to assure a superficial protection.

Data sheet mod. 3058







Description

Semi-clean cut nippers, very heavy, for the cutting of steel wires up to \emptyset 1.5 mm.

L	151
T	12
В	17