



Part Number:

510

Type	Size	Rating	Description
Incandescent	T10	12V 2.2W	T-3¼ Wedge Base Lamp



Dimensions in millimetres

TEST VOLTS	CURRENT (mA)			LIGHT OUTPUT (Lm)			LIFE Hours
	Min.	Nom.	Max.	Min.	Nom.	Max.	
13	168	192	216	9.4	12.6	15.7	3000

Notes:

- Base Type** W2.1x9.5d in accordance with BSEN60061-1
- Filament Shape** C-2V
- Bead colour** White or clear
- Lamp Marking** CML 510 12V 2.2W
- Environmental** RoHS & REACH SVHC compliant