

Block sanding disc

shape 1, ceramic bonded

ORION[®]

Application:

Maximum operating speed: 40 m/s. Not suitable for wet grinding.

Advantage:

- smooth running
- in stackable individual packaging
- Includes Reducing ring

Delivery:

Bore diameter 32 mm = reduction 32/20/16 -

Bore diameter 51 mm = reduction 51/32 -

Bore diameter 76 mm = reduction 76/40



Art. no.	69496 255
Brand	ORION
Manufacturer Part Number	69496255
Washer diameter	200 mm
Washer thickness	25 mm
Material to be processed	Cast metal, Carbide
Form	1
Material of abrasive medium	Green silicon carbide
Surface structure	Fine
Grid size	80
Binding	Ceramically bound
Bore diameter	51 mm
ISO	525
Number of pieces per packet	1
Machining method	Tool grinding
Gross Weight	1.705 kg
Product Group	6LO

EAN

4053625330317