SIEMENS

Data sheet for SINAMICS G120X

Article No. :

6SL3220-3YE18-0AF0



Figure similar

Client order no. :
Order no. :
Offer no. :
Remarks :

Rated	d data	
Input		
Number of phases	3 AC	
Line voltage	380 480 V +10 %	% -20 %
Line frequency	47 63 Hz	
Rated voltage	400V IEC	480V NEC
Rated current (LO)	6.90 A	5.80 A
Rated current (HO)	5.50 A	4.60 A
Output		
Number of phases	3 AC	
Rated voltage	400V IEC	480V NEC ¹⁾
Rated power (LO)	3.00 kW	4.00 hp
Rated power (HO)	2.20 kW	3.00 hp
Rated current (LO)	7.70 A	6.20 A
Rated current (HO)	5.90 A	4.80 A
Rated current (IN)	8.00 A	
Max. output current	9.10 A	
Pulse frequency	4 kHz	
Output frequency for vector control	0 200 Hz	
Output frequency for V/f control	0 550 Hz	

Overload capability

Low Overload (LO)

110% base load current IL for 60 s in a 300 s cycle time

High Overload (HO)

150% x base load current IH for 60 s within a 600 s cycle time

General tech. specifications		
Power factor λ	0.70 0.85	
Offset factor $\cos \phi$	0.96	
Efficiency η	0.97	
Sound pressure level (1m)	55 dB	
Power loss ³⁾	0.125 kW	
Filter class (integrated)	RFI suppression filter for Category C2	
EMC category (with accessories)	Category C2	
Safety function "Safe Torque Off"	without	

Communication

Communication

PROFINET, EtherNet/IP

ltem no. : Consignment no. : Project :

Standard digital inputsNumberSwitching level: $0 \rightarrow 1$ Switching level: $1 \rightarrow 0$ Max. inrush currentFail-safe digital inputs	6 11 V 5 V 15 mA 1 2
Switching level: $0 \rightarrow 1$ Switching level: $1 \rightarrow 0$ Max. inrush current	11 V 5 V 15 mA
Switching level: $1 \rightarrow 0$ Max. inrush current	5 V 15 mA
Max. inrush current	15 mA
	1
Fail-safe digital inputs	
Number	2
Digital outputs	2
Number as relay changeover contact	Z
Output (resistive load)	DC 30 V, 5.0 A
Number as transistor	0
Analog / digital inputs	
Number	2 (Differential input)
Resolution	10 bit
Switching threshold as digital input	
0 → 1	4 V
1 → 0	1.6 V
Analog outputs	
Number	1 (Non-isolated output)
PTC/ KTY interface	
1 motor temperature sensor input, sens Thermo-Click, accuracy ± 5 °C	sors that can be connected PTC, KTY and

Closed-loop control techniques	
V/f linear / square-law / parameterizable	Yes
V/f with flux current control (FCC)	Yes
V/f ECO linear / square-law	Yes
Sensorless vector control	Yes
Vector control, with sensor	No
Encoderless torque control	No
Torque control, with encoder	No

SIEMENS

Data sheet for SINAMICS G120X

Article No. :

6SL3220-3YE18-0AF0

Ambie	ent conditions
Standard board coating type	Class 3C2, according to IEC 60721-3-3: 2002
Cooling	Air cooling using an integrated fan
Cooling air requirement	0.005 m³/s (0.177 ft³/s)
Installation altitude	1,000 m (3,280.84 ft)
Ambient temperature	
Operation	-20 45 °C (-4 113 °F)
Transport	-40 70 °C (-40 158 °F)
Storage	-25 55 °C (-13 131 °F)
Relative humidity	
Max. operation	95 % At 40 °C (104 °F), condensation and icing not permissible
Co	onnections
Signal cable	
Conductor cross-section	0.15 1.50 mm² (AWG 24 AWG 16)
Line side	
Version	screw-type terminal
Conductor cross-section	1.50 2.50 mm² (AWG 16 AWG 14)
Motor end	
Version	Screw-type terminals
Conductor cross-section	1.50 2.50 mm ² (AWG 16 AWG 14)
DC link (for braking resistor)	
PE connection	On housing with M4 screw
Max. motor cable length	
· · · · · · · · · · · · · · · · · · ·	
Shielded	150 m (492.13 ft)

echanical data	
IP20 / UL open	type
FSA	
3.4 kg (7.50 lb)
73 mm (2.87 i	n)
232 mm (9.13	in)
218 mm (8.58	in)
Standards	
	Tick (RCM), EAC, KCC, CH
	2004/108/EC, Low- ive 2006/95/EC
osses to IEC61800-	9-2*
IE2	
36.8 %	
100.0 W (1.9 %)	125.0 W (2.4 %)
Ť	Ţ
70.2 W (1.3 %)	79.1 W (1.5 %)
•••••	•
50.2111 (1.1.11)	
•	
1	1
	IP20 / UL open FSA 3.4 kg (7.50 lk 73 mm (2.87 i 232 mm (9.13 218 mm (8.58 Standards UL, cUL, CE, C- SEMI F47, REA EMC Directive Voltage Direct Disses to IEC61800- IE2 36.8 %

The percentage values show the losses in relation to the rated apparent power of the converter.

90% **f**

50%

The diagram shows the losses for the points (as per standard IEC61800-9-2) of the relative torque generating current (I) over the relative motor stator frequency(f). The values are valid for the basic version of the converter without options/components.

*converted values

¹⁾The output current and HP ratings are valid for the voltage range 440V-480V

³⁾Typical value. More information can be found in the element group "Converter losses to IEC 61800-9-2" in this datasheet.

SIEMENS

Data sheet for SINAMICS G120X

Article No. :

6SL3220-3YE18-0AF0

	Operator panel: Intell	igen
	Screen	7
Display design	LCD color	_
Screen resolution	320 x 240 Pixel	
		7
	Mechanical data	
Degree of protection	IP55 / UL type 12	
Net weight	0.134 kg (0.30 lb)	
Dimensions		
Width	70.00 mm (2.76 in)	
Height	106.85 mm (4.21 in)	
Depth	19.65 mm (0.77 in)	

Ambient conditions Ambient temperature		
	55 °C only with door installation kit	
Storage	-40 70 °C (-40 158 °F)	
Transport	-40 70 °C (-40 158 °F)	
Relative humidity at 25°C durir	ng	
Max. operation	95 %	
	Approvals	