


**MX1300** 

Size: D (LR20)


# **Alkaline-Manganese Dioxide Battery**





Nominal Voltage:	1.5 V
Operating Voltage	1.6 -0.75V
Impedance:	125 m-ohm @ 1kHz
Typical Weight:	145 gm (5.1 oz.)
Typical Volume:	56.4 cm <sup>3</sup> (3.4 in. <sup>3</sup> )
Terminals:	Flat
Storage Temperature Range:	-20 °C to 35 °C
Operating Temperature Range:	-20 <sup>o</sup> C to 54 <sup>o</sup> C (-4 <sup>o</sup> F to 130 <sup>o</sup> F)
ANSI: IEC:	13A LR20

# TYPICAL DISCHARGE CHARACTERISTICS AT 21° C (70°F)



# **DURACELL**® BATTERIES

Berkshire Corporate Park Bethel, CT 06801 U.S.A.

Telephone: Toll-free 1-800-544-5454

Internet: www.duracell.com


<sup>\*</sup> Delivered capacity is dependent on the applied load, operating temperature and cut-off voltage. Please refer to the charts and discharge data shown for examples of the energy / service life that the battery will provide for various load conditions.

**MX1300** 


Size: D (LR20)

## **Alkaline-Manganese Dioxide Battery**

#### DELIVERED ENERGY VS POWER DRAIN




#### SERVICE HOURS VS POWER DRAIN



# DURACELL® ULTRA POWER

### DELIVERED CAPACITY VS POWER DRAIN



All testing at 21  $^{\circ}$ C (70 F)



Berkshire Corporate Park Bethel, CT 06801 U.S.A.

Telephone: Toll-free 1-800-544-5454

Internet: www.duracell.com

<sup>\*</sup> Delivered capacity is dependent on the applied load, operating temperature and cut-off voltage. Please refer to the charts and discharge data shown for examples of the energy / service life that the battery will provide for various load conditions.