



# Temperature Sensors

## Thermoresistances


► (RTS) Bayonet Bore Type with Silicone Cable



► (RTST) Bayonet Bore Type with Teflon Cable



► (RTSM) Bayonet Bore Type with Braided Wire Cable



► (RTSKP5) Bayonet Type with Cable Lug



- Max. operating temperature : **400°C** for Braided wire, **200°C** for Silicone, **260°C** for Teflon
- Standard cable types : Fiber glass + Fiber glass + Braided wire, 3x0,22 mm<sup>2</sup> / Silicone + Silicone, 3x0,22 mm<sup>2</sup> / Teflon + Teflon, 3x0,22 mm<sup>2</sup>
- Standard cable length (K) : K01 = 1mt, K02 = 2mt, K03 = 3 mt, K04 = 4mt, K05 = 5 mt.
- Sensor type : DIN/EN60751 Class "B" 1xPt-100 for **E=1** or 2xPt-100 for **E=2**
- Protection tube material : AISI304 (DIN1.4301), AISI316 Order Code "316"