



Partition, ventilated, for power feeder, WxD = 800 x 600 mm

Part no. XTPPCCH2-W800D600
Article no. 178395

Technical data ETIM 6.0

Cabinet enclosures (EG000011) / Divider panel (switchgear cabinet) (EC002525)		
Electric engineering, automation, process control engineering / Electrical cabinet, housing, rack / Panel (electrical cabinet) / Divider panel (electrical cabinet) (ecl@ss8.1-27-18-21-02 [AKE424011])		
Modular spacing	mm	12.5
Suitable for enclosure building width	mm	800
Suitable for enclosure building depth	mm	600
Width	mm	787
Height	mm	49
Material		Steel
Type of surface		Zinc coated
Colour		Stainless steel
RAL-number		0
With cable entry		No
Number of height units		0
With lock		No
Construction type		Individual part
For internal partitioning shape 2a		Yes
For internal partitioning shape 2b		Yes
For internal partitioning shape 3a		Yes
For internal partitioning shape 3b		Yes
For internal partitioning shape 4a		Yes
For internal partitioning shape 4b		Yes