

SAFETY DATA SHEET

according to Regulation (EU) 2020/878

Page 1/8

Sample Handling Products - Letheen Broth

Revision 0 Revision date 2023-12-08

	Revision date 2023-12
SECTION 1: Identification	of the substance/mixture and of the company/undertaking
1.1. Product identifier	
Product name Product code	Sample Handling Products - Letheen Broth 700002009, 700002010, 700002012, 700002039, 700002044, 700002047, 700002108, 700002109, 700002205, 700002206
1.2. Relevant identified uses of	of the substance or mixture and uses advised against
Product Use	[SU3] Industrial uses: Uses of substances as such or in preparations at industrial sites; [PC21] Laboratory chemicals;
Description	Intended for use in routine analytics, including quality control and monitoring.
1.3. Details of the supplier of t	he safety data sheet
Company Address	Neogen Corporation 620 Lesher Place Lansing MI 48912 USA
Web	www.neogen.com
Telephone	517-372-9200/800-234-5333
Email	SDS@neogen.com
1.4. Emergency telephone nui	mber
	24 hours: Medical: 1-800-498-5743 (U.S. and Canada) or 1-651-523-0318 (international) Spill/CHEMTREC: 1-800-424-9300 (U.S. and Canada) or 1-703-527-3887 (international)
SECTION 2: Hazards iden	tification
2.1. Classification of the subst	ance or mixture
2.1.2. Classification - EC 1272/2008	Based on available data, this product is not classified as hazardous.
2.2. Label elements	
Hazard Statement	No Significant Hazard
2.3. Other hazards	
Other hazards	None known.
SECTION 3: Composition/	information on ingredients
Description	
	No components need to be disclosed according to the applicable regulations. Concentrations listed are not product specifications.
Particle Characteristics	
	Not applicable.

Revision 0 **Revision date** 2023-12-08

	Revision date 2023-12-0
Further information	
	Full text of Hazard Statements listed in this Section is provided in Section 16.
SECTION 4: First aid meas	sures
4.1. Description of first aid me	asures
Inhalation	Move the exposed person to fresh air. If breathing is difficult give oxygen. If breathing stops, provide artificial respiration. Seek medical attention if irritation or symptoms persist.
Eye contact	Rinse immediately with plenty of water. Contact lenses should be removed. Seek medical attention if irritation or symptoms persist.
Skin contact	Remove contaminated clothing. Wash with soap and water. Seek medical attention if irritation or symptoms persist.
Ingestion	Do not induce vomiting unless told to do so by the poison control center or doctor. Rinse mouth thoroughly. Never give anything by mouth to an unconscious person. Get medical advice/attention if you feel unwell.
4.2. Most important symptoms	and effects, both acute and delayed
Inhalation	May cause irritation to respiratory system.
Eye contact	May cause irritation to eyes.
Skin contact	May cause irritation to skin.
Ingestion	Ingestion may cause nausea and vomiting.
4.3. Indication of any immedia	te medical attention and special treatment needed
	Remove the affected person from the source of contamination immediately. Transfer to hospital if there are burns or symptoms of poisoning. Seek medical attention if irritation or symptoms persist. If medical advice is needed, have product container or label at hand.
SECTION 5: Firefighting m	easures
5.1. Extinguishing media	
	Use extinguishing media appropriate to the surrounding fire conditions.
5.2. Special hazards arising fro	om the substance or mixture
	Product does not support combustion. Do not allow undiluted product to be released to ground water, water course or sewage system.
5.3. Advice for firefighters	
	Do not breathe vapour or spray mist. Wear self-contained breathing apparatus and chemical-protective clothing.
SECTION 6: Accidental rel	ease measures
	tective equipment and emergency procedures
	Use as appropriate: Protective equipment, Protective clothing. Ensure adequate ventilation of the working area. Avoid prolonged or repeated exposure.
6.2. Environmental precaution	
·	Prevent further spillage if safe. Clean spillage area thoroughly with plenty of water. Do not flush into surface water. Do not let product contaminate subsoil.
6.3. Methods and material for containment and cleaning up	
	Absorb spillage to prevent material damage. Clean spillage area thoroughly with plenty of water. Do not contaminate water by cleaning of equipment or disposal of wastes.
6.4. Reference to other section	ns
	See Section(s) 2, 8, and 13 for further information.

SECTION 7: Handling and storage

Revision 0 Revision date 2023-12-08

7.1. Precautions for safe handling

Adopt best Manual Handling considerations when handling, carrying and dispensing. Avoid contact with eyes. Do not eat, drink or smoke in areas where this product is used or stored. Ensure adequate ventilation of the working area. Do not contaminate water by cleaning of equipment or disposal of wastes. Use as appropriate: Protective clothing. Read the entire label and follow all use directions, restrictions, and precautions.

7.2. Conditions for safe storage, including any incompatibilities

Store at temperatures between 2 °C and 30 °C. Follow label instructions. Store in correctly labelled containers. Keep container tightly closed. Do not contaminate water, food, or feed by storage or disposal.

7.3. Specific end use(s)

See Section(s) 1.2 for further information.

Further information

Refer to product label and/or package insert for additional information. Follow label instructions.

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

No occupational exposure limits known.

8.2. Exposure controls







8.2.1. Appropriate engineering controls

8.2.2. Individual protection measures

Eye / face protection

Skin protection -Handprotection

Skin protection - Other

Respiratory protection

Occupational exposure controls

Ensure adequate ventilation of the working area.

Use as appropriate: Protective equipment.

Use as appropriate: Suitable eye protection.

Use as appropriate: Chemical-resistant gloves made of any waterproof material. Wash the outside of gloves before removing them.

Use as appropriate: Protective clothing. Wash contaminated clothing, separately from other laundry, with detergent and water before reuse.

In case of insufficient ventilation, wear suitable respiratory equipment.

Exposure above the recommended occupational exposure limit (OEL) may cause adverse health effects. Protect clothing from contact with the product. Provide chemical shower. Provide eye wash

Further information

Remove and wash contaminated clothing before reuse.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Revision 0 Revision date 2023-12-08

9.1. Information on basic physical and chemical properties

Appearance	Liquid
Colour	
Odour	Slight
Odour threshold	No data available
pH	No data available
Melting point	No data available
Freezing Point	No data available
Initial boiling point	No data available
Flash point	No data available
Evaporation rate	No data available
Flammability (solid, gas)	Not applicable.
Vapour pressure	No data available
Relative Vapour Density	No data available
Density / Relative Density	No data available
Fat Solubility	No data available
Partition coefficient (P)	No data available
Autoignition temperature	Not applicable.
Viscosity	No data available
Explosive properties	Not applicable.
Oxidising properties	No data available
Solubility	Soluble in water

9.2. Other information

Conductivity	No data available
Surface tension	No data available
Gas group	No data available
Benzene Content	No data available
Lead content	No data available
VOC (Volatile organic	No data available
compounds)	

SECTION 10: Stability and reactivity

10.1. Reactivity

Stable under normal conditions.

10.2. Chemical stability

Stable under normal conditions.

10.3. Possibility of hazardous reactions

Under the specified conditions, hazardous reactions that lead to excessive temperatures or pressure are not expected.

10.4. Conditions to avoid

Keep away from extreme temperatures.

10.5. Incompatible materials

No data available.

10.6. Hazardous decomposition products

Carbon oxides.

SECTION 11: Toxicological information

Revision 0 **Revision date** 2023-12-08

11.1 Information on hazard classes

	Ses
Acute toxicity	Based on available data, the classification criteria are not met.
Skin corrosion/irritation	May cause irritation to skin.
Serious eye damage/irritation	May cause irritation to eyes.
Respiratory or skin sensitisation	May cause allergic reactions in susceptible people.
Germ cell mutagenicity	No mutagenic effects reported.
Carcinogenicity	No components at >0,01% are listed in the American Conference of Governmental Industrial Hygienists (ACGIH) Guide to Occupational Exposure Values. No components at >0.01% are listed in the International Agency for Research on Cancer (IARC) Monographs. No components at >0,01% are listed in the National Toxicology Program (NTP) Report on
	Carcinogens.
Poproductive toxicity	Not listed in the OSHA standard 1910.1003 Carcinogens.
Reproductive toxicity	No teratogenic effects reported.
STOT-single exposure	May cause allergy or asthma symptoms or breathing difficulties if inhaled.
STOT-repeated exposure	No Significant Hazard.
Aspiration hazard	No Significant Hazard.
Repeated or prolonged exposure	Avoid prolonged or repeated exposure. Delayed appearance of the complaints and development of hypersensitivity (difficult breathing, coughing, asthma) are possible.
11.1.2. Mixtures	
	See Section(s) 3 for further information.
11.1.3. Hazard Information	
	See Section(s) 2 and 3 for further information.
11.1.4. Toxicological Information	'
	No data available
11.1.5. Hazard Class	
	See Section(s) 2 and 14 for further information.
11.1.6. Classification Criteria	
	Based on the Globally Harmonised System (GHS) considerations for the classification of mixtures. See Section 15 for regulatory citations.
11.1.7. Information on likely rout	es of exposure
	Eye contact. Skin contact. Ingestion. Inhalation.
11.1.8. Symptoms related to the	physical, chemical and toxicological characteristics
	See Section(s) 4.2 for further information.
11.1.9. Delayed and immediate	effects as well as chronic effects from short and long-term exposure
	See Section(s) 4.2 for further information.
11.1.10. Interactive effects	
	No data available.
11.1.11. Absence of specific dat	a
	<1% of this mixture consists of ingredients of unknown acute toxicity.
11.1.12. Mixture versus substan	ce information
	See Section(s) 3 for further information.
11.1.13. Other information	

Revision 0 Revision date 2023-12-08

11.1.13. Other information	
	No data available.
11.2 Information on other hazard	ds
	No data available.
SECTION 12: Ecological info	ormation
12.1. Toxicity	
	No data available
12.2. Persistence and degradab	ility
	No data is available on this product.
12.3. Bioaccumulative potential	
	No data is available on this product.
12.4. Mobility in soil	
	No data is available on this product.
12.5. Results of PBT and vPvB	assessment
	No data is available on this product.
12.6 Endocrine disrupting prope	rties
	No data is available on this product.
12.7 Other adverse effects	
	Specific test data for the mixture is not available.
Further information	
	Keep out of lakes, ponds, or streams. Do not let product contaminate subsoil.
SECTION 13: Disposal cons	iderations
13.1. Waste treatment methods	
	Dispose of in compliance with all local and national regulations. Follow label instructions.
Disposal methods	
	Do not contaminate water by cleaning of equipment or disposal of wastes. Do not flush into surface
	water. Dispose of in compliance with all local and national regulations.
Disposal of packaging	
	Nonrefillable container. Do not reuse or refill this container.
	If empty: Do not reuse this container. Place in trash or offer for recycling, if available.
	If partly filled: Call your local solid waste agency for disposal instructions. Never place unused product down any indoor or outdoor drain.
SECTION 14: Transport info	
14.1. UN number	
	The product is not classified as dangerous for carriage.
14.2. UN proper shipping name	
	The product is not classified as dangerous for carriage.
14.3. Transport hazard class(es)	
	The product is not classified as dangerous for carriage.
14.4. Packing group	

Revision 0 **Revision date** 2023-12-08

14.4. Packing group	
	The product is not classified as dangerous for carriage.
14.5. Environmental hazards	
	The product is not classified as dangerous for carriage.
14.6. Special precautions for user	
	The product is not classified as dangerous for carriage.
14.7 Maritime Transport in bulk according to IMO instruments	
	The product is not classified as dangerous for carriage.
SECTION 15: Regulatory information	

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Regulations	COMMISSION REGULATION (EU) 2020/878 of 18 June 2020 amending Annex II to Regulation (EC) No 1272/2008 of the European Parliament and of the Council concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH).
Chemical Inventories/Right-to-Know Lists:	Contact SDS@neogen.com for additional information. Please specify country or region with your request.
	California Proposition 65: This product does not contain reportable substances at >0,0001% concentration.

SECTION 16: Other information

Other information

Acronyms	ADR/RID: European Agreements Concerning the International Carriage of Dangerous Goods by Rail (RID) and by Road (ADR).
	CAS No.: Chemical Abstracts Service.
	CLASS: Classification, Labelling, and Safety Data Sheet of Hazardous Chemicals Regulation 2013 (Malaysia).
	FIFRA: U.S. Federal Insecticide, Fungicide, and Rodenticide Act.
	GHS: Globally Harmonized System.
	HCS 2012: U.S. Hazard Communication Standard (2012 revision).
	IATA: International Air Transport Association.
	ICAO: International Civil Aviation Organisation.
	IMDG: International Maritime Dangerous Goods.
	LD: Lethal dose.
	OEL: Occupational exposure limit.
	OSHA: U.S. Occupational Safety and Health Administration.
	PEL: Permissible Exposure Limit.
	REACH: Registration, Evaluation, Authorisation, and Restriction of Chemicals.
	STOT: Specific Target Organ Toxicity.
	SVHC: Substance of very high concern.
	US DOT: United States Department of Transportation.
	VOC: Volatile Organic Compound.
	WEL: Workplace Exposure Limit.
Further information	

DISCLAIMER: The information and recommendations set forth herein ("Information") are presented in good faith and believed to be correct as of the date issued. No representation is made regarding the completeness or accuracy of the Information. Further, because of the many factors that affect the use of this product, the Information is supplied upon the condition that the person(s) receiving it will make their own determination regarding its suitability for their own unique purpose(s), prior to use.

Page 8/8

Sample Handling Products - Letheen Broth

Revision 0 Revision date 2023-12-08

Further information	
	Except as expressly stated herein, NO WARRANTIES, GUARANTEES, OR REPRESENTATIONS
	OF ANY KIND, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, IMPLIED
	WARRANTY OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, COURSE OF
	PERFORMANCE, USAGE OF TRADE, OR RESULTS TO BE OBTAINED BY USE OF THIS
	PRODUCT are made with respect to this product or use of this product. The product covered is
	furnished "as is" and only subject to the warranties herein provided, no liability is assumed
	resulting from the use of this product.