XVBC33 INDICATING BANK LENS 250V 10W +OPTIONS



Main

		suo
		applications
		dde .
Main		c user
Range of product	Harmony XVB Universal	 specific
Product or component type	Indicator bank	for sp
Beacon or indicator bank unit type	Illuminated unit	products
Signalling type	Steady	
Mounting diameter	70 mm	these
Component name	XVBC	lity of
Material	Polycarbonate	eliability
Light source	Green bulb not included	or
Bulb type	Incandescent with BA 15d base Protected LED	suitability
[Us] rated supply voltage	<= 250 V	nining

Complementary

[Us] rated supply voltage	<= 250 V	
Complementary		
Assembly style	Customer assembly, up to 5 units	
Power dissipation in W	<= 7 W	
Connections - terminals	Screw clamp terminals : <= 1 x 1.5 mm ² with cable end	
[Ui] rated insulation voltage	250 V conforming to IEC 60947-1	
Nominal voltage limit	0.851.1 Un conforming to IEC 60947-5-1	
[Uimp] rated impulse withstand voltage	4 kV conforming to IEC 60947-1	
CAD overall width	70 mm	
CAD overall height	63 mm	
CAD overall depth	70 mm	
E. Survey		
Environment		
Pollution degree	2	
Product certifications	GOST	
	CSA C22-2 No 14	
	CCC	
	UL 508	

Environment

Pollution degree	2	3
Product certifications	GOST CSA C22-2 No 14 CCC UL 508	in the second

Standards	EN/IEC 60947-5-1	
Protective treatment	TC	
Ambient air temperature for storage	-4070 °C	
Ambient air temperature for operation	-2550 °C, with LED -2570 °C, with incandescent	
Class of protection against electric shock	Class I on support tube conforming to IEC 61140 Class II on base unit conforming to IEC 61140	
IP degree of protection	IP65 on fixing base XVBZ0. conforming to IEC 60529 IP66 on base unit conforming to IEC 60529	
NEMA degree of protection	NEMA 4X indoor conforming to UL 508	

18 months


Contractual warranty

Warranty period

Indicator Bank without "Flash" Discharge Tube Unit

Dimensions

Below drawing shows the minimum configuration of the product. Select the number of stages according to the product characteristics in order to get b dimension.




- (1) Base unit XVBC21, to be ordered separately
- (2) Illuminated or audible signalling unit
- (3) Cover (supplied with XVBC21 base unit)

Number of illuminated or audible signalling units (no "flash")	b in mm	b in in.
1	138	5.43
2	201	7.91
3	264	10.39
4	327	12.87
5	390	15.35

Indicator Bank with "Flash" Discharge Tube Unit

Dimensions

Below drawing shows the minimum configuration of the product. Select the number of stages according to the product characteristics in order to get b dimension.



- (1) Base unit XVBC07, to be ordered separately
- Illuminated or audible signalling unit
- (2) (3) "Flash" unit, to be ordered separately

Number of illuminated or audible signalling units other than "flash" tube	b in mm	b in in.
1	295	11.61
2	358	14.09
3	421	16.57
4	484	19.06