

Product information

64 52 115

Electronics End Cutting Nipper

DIN ISO 9654



- Precision pliers for ultra fine cutting work, e. g. in electronics and fine mechanics
- Sturdy, zero backlash box joint
- Low-friction double spring for gentle and even opening
- The polish or mirror polish together with a fine film of oil offer effective rust protection - no circuit faults caused by peeling chrome from plated tools
- Cutters additionally laser hardened, cutter hardness at least 56 HRC
- Oblique End Cutter, short head, without bevel, for flush cutting, $\alpha = 27^\circ$
- Ball bearing chrome steel, oil hardened



General

Article No.	64 52 115
EAN	4003773040439
Head	mirror polished
Handles	with multi-component grips
Weight	70 g
Dimensions	115 x 68 x 17 mm
Standard	DIN ISO 9654
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details

Cutting capacities soft wire (diameter)	Ø 1.3 mm
Head width (A)	11 mm
Jaw length (B)	10 mm
Jaw thickness (joint) (D)	7 mm
Cutting edge length mm (C)	12 mm

technical change and errors excepted

