

758-25

Torque screwdriver Type SP

10-500 cN·m / 14 ozf·in-40 lbf·in

Code	ETIM
7096540	None
EAN	UNSPSC
4002805758250	27-11-17-15
Country of Origin	eCl@ss
England	21-04-32-90
Customs tariff no.	
82041100	



Article description

- Use:
- In the torque range 0.1 - 5.0 N·m
- For test and installation work in the electrical and electronic hardware industry, instrument-making industry and industrial manufacturing or in quality control
- Features:
- Dial-indicating torque and test screwdriver - with dual scale (cN·m/ozf·in/lbf·in)
- With 1/4" female hexagon drive for use with 1/4" hexagon bits as per DIN 3126 - C 6.3
- With adaptor also suitable for 1/4" square drive sockets as per DIN 3124
- Display accuracy: +/- 6 % tolerance of the indicated value
- Acc. to DIN EN ISO 6789, traceable to national standards
- For controlled bi-directional tightening
- With slave-pointer function
- For locking of maximum values / maximum-value display
- 4 models in the range 0,1 N·m to 5,0 N·m
- Lightweight construction by virtue of anodised aluminium handgrips
- EPA-conformant (Electrostatic Protected Area), for use in sensitive electrostatic applications
- Scope of delivery:
- Torque screwdriver Type 758
- 1/4" square/hexagon drive adaptor (No. 757-20)
- Models 758-25/-50 with additional sliding T-bar for ease of use
- Test certificate acc. to DIN EN ISO 6789
- Delivery in sturdy cardboard packaging

Article information

Contents (Qty of pieces)	1 tlg.	Drive connector hexagon female (metric)	6,3 mm
Total length [mm]	250 mm	Net weight [kg]	0,465 kg
Torque (min.) [N·m]	0,5 N·m	Torque (max.) [cN·m]	250 cN·m
Torque (max.) [N·m]	2,5 N·m	Torque (min.) [cN·m]	50 cN·m
Total height [mm]	64 mm	Torque (max.) [lbf·in]	4 lbf·in
Drive connector hexagon female [inch]	1/4"	Torque (min.) [lbf·in]	20 lbf·in