

## Han Q 2/0-f-crimp



Image is for illustration purposes only. Please refer to product description.

Part number	09 12 002 3151
Specification	Han Q 2/0-f-crimp
HARTING eCatalogue	<a href="https://b2b.harting.com/09120023151">https://b2b.harting.com/09120023151</a>

### Identification

Category	Inserts
Series	Han <sup>®</sup> Q
Identification	2/0

### Version

Termination method	Crimp termination
Gender	Female
Size	3 A
Number of contacts	2
PE contact	Yes
Details	Please order crimp contacts separately.

### Technical characteristics

Conductor cross-section	1.5 ... 10 mm <sup>2</sup>
Rated current	40 A
Rated voltage	400 V
Rated impulse voltage	6 kV
Pollution degree	3
Rated voltage acc. to UL	600 V
Rated voltage acc. to CSA	600 V
Insulation resistance	>10 <sup>10</sup> Ω
Limiting temperature	-40 ... +125 °C



Pushing Performance  
Since 1945

## Technical characteristics

Mating cycles	≥500
---------------	------

## Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

## Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076 UL 2237 PVVA2.E318390 CSA-C22.2 No. 182.3 PVVA8.E318390
Approvals	DNV GL

## Commercial data

Packaging size	10
Net weight	7.2 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140016729
ETIM	EC000438
eCl@ss	27440205 Contact insert for industrial connectors