

## MM 12 high-performance multi-purpose measuring instrument

Wireless Logging TRUE RMS Digital Multimeter

**BENNING**

### Application:

For demanding measuring tasks in industry and craftsmanship

### Delivery:

incl. PC software, serial data cable with USB connection, protective rubber frame, magnetic hanger, case, batteries, test leads, wire temperature sensor and calibration certificate



<b>Art. no.</b>	<b>75024 245</b>
<b>Brand</b>	BENNING
<b>Manufacturer Part Number</b>	44088
<b>Model</b>	MM 12
<b>Display range</b>	4000 digits, 40000 digits
<b>Measuring accuracy</b>	+/- 0.5 %
<b>Min./max. test voltage (DC)</b>	10 $\mu$ V/DC-1000 V/DC
<b>Min./max. test voltage (AC)</b>	10 $\mu$ V/AC-1000 V/AC
<b>Min./max. alternating current of measuring range</b>	10 $\mu$ A-10 A
<b>Min./max. direct current of measuring range</b>	10 $\mu$ A-10 A
<b>Continuity testing</b>	Yes
<b>Diode testing</b>	Yes
<b>Min./max. electrical-resistance measuring range</b>	0.1 Ohm-40 MOhm
<b>Min./max. frequency</b>	0.0001 / 100 kHz
<b>Min./max. temperature measuring range</b>	-200 to 1200 °C
<b>Volt sensor</b>	Yes
<b>Memory function</b>	HOLD, PEAK-HOLD, MAX/MIN/AVG, REL
<b>Measuring procedure</b>	TRUE RMS AC, AC+DC
<b>Overvoltage protection category</b>	CAT IV/600 V, CAT III/1000 V
<b>Length x width x height</b>	206 x 94 x 54 mm
<b>EN standard</b>	61010
<b>Gross Weight</b>	1.277 kg
<b>Product Group</b>	7AH

### EAN

4014651440883