Ferromagnetic Metal Detection Sensors

#### **DESCRIPTION**

These reed proximity switches operate when in the presence of magnetically conductive material. Instead of an actuating magnet, only a simple piece of iron is required to operate the sensor from the front or from above. The standard cable is UL listed and is round twin core 2 x 0.35 mm² (AWG22).

### **FEATURES**

- Form A and B are available
- · High power switches available
- · Other cables, connectors and colors available
- A choice of cable terminations and lengths are available





### **APPLICATIONS**

- Industrial applications
- End travel sensing limit switch in pneumatic cylinders
- Position control
- · Control functions in plant and utility vehicles
- Security applications
- Door and window control
- · Opening recognition contact
- Fire protection doors

#### **DIMENSIONS**

All dimensions in mm [inches]





## **ORDER INFORMATION**

Part Number Example

MK2/0 - 1A66 - 500 W

MK2/0 is the front operation series 1A is the contact form 66 is the switch model 500 is the cable length (mm) W is the termination

	SERIES	CONTACT FORM	SWITCH MODEL	CABLE LENGTH(mm)	TERMINATION	
	MKX/X -	XX	XX -	xxx	×	
	2/0, 2/1	1 Form A	66			
OPTIONS	2/2*, 2/3*	1 Form B	90	500 **	S*, W, X, Y, U	
	2/5	1 Form A	41			


<sup>S option only available with 22/ and 2/3.
Other cable length available.</sup> 

# www.meder.com


Ferromagnetic Metal Detection Sensors

## **OPERATION EXAMPLE**

For best operation it is recommended that you **<u>DO NOT</u>** mount these sensors on any ferromagnetic material **<u>OR</u>** use any ferromagnetic screws.



The MK2/2 and 2/3 are available as Form A and Form B sensors. The standard cable is a 4-wire round - core 4 x 0.14  $\rm mm^2$  (cable sheath and wires are white) forming a sabotage loop. See example of this loop to the right.



(Sabotage loop for MK2/2 and 2/3.)

## **TERMINATION**

For wire and termination details please consult factory.

S	The cable cut length includes: 30 mm of exposed insulated wire with 5 mm of wire stripped and tinned
W	The cable cut length includes: 30 mm of exposed insulated wire with 5 mm of wire stripped and tinned
X	The cable cut length includes: 30 mm of exposed insulated wire with individual crimped terminals
Υ	The cable cut length includes: 30 mm of exposed insulated wire with individual spade terminals
U	Cable with click sensor-connector (3 pole, M8)

Ferromagnetic Metal **Detection Sensors** 

# **CONTACT DATA**

	1										
All data at 20 °C	Switch Model> Contact Form>	5	Switch A		S	Switch Form /			witch ( Form E		
Contact Ratings	Conditions	Min.	Тур.	Max.	Min.	Тур.	Max.	Min.	Тур.	Max.	Units
Switching Power	Any DC combination of V & A not to exceed their individual max			16			10			3	W
Switching Voltage	DC or peak AC			40			200			175	V
Switching Current	DC or peak AC			0.4			0.5			0.25	Α
Carry Current	DC or peak AC			0.7			1.25			1.2	Α
Static Contact Resistance	w/ 0.5 V & 50 mA			100			150			150	mΩ
Dynamic Contact Resistance	w/ 0.5 V & 50 mA			150			200			250	mΩ
Insulation Resistance (100 Volts applied)	Across contacts Contact to coil	10 <sup>9</sup>			10 <sup>10</sup> *			10 <sup>9</sup>			Ω
Breakdown Voltage	> 60 sec	150			225*			200			VDC
Operate Time, incl. Bounce	Measured w/ 100 % overdriv			0.7			0.5			0.7	ms
Reset Time	Measured w/ no coil suppression			0.05			0.1			1.5	ms
Capacitance	Across contacts Contact to coil		0.3			0.2			1.0		pF
Contact Operation**											
Must Operate Condition		8		12	4.5		10	3.0		8.5	mm
Must Release Condition		10		16	5.5		13.5	4.0		12	mm
Environmental Data											
Shock Resistance	1/2 sine wave duration 11ms			30			30			50	g
Vibration Resistance	From 10 - 2000 Hz			10			10			20	g
Amvient Temperature	10 °C/ minute max. allowable	-20		80	-20		85	-20		85	°C
Storage Temperature	10 °C/ minute max. allowable	-20		80	-35		85	-35		85	°C
Soldering Temperature	5 sec. dwell						260			260	۰C

Please note: The indicated data are maximum values and can vary downwards when using a more sensitive switch.

\* Insulation resistance of 10<sup>12</sup> and breakdown voltage of 480 VDC is available.

\*\* These ranges refer to the uncut / unmodified Reed Switches described in our Reed Switch section. Consult factory if more details is required.




Headquarter Europe MEDER electronic AG Friedrich-List Strasse 6 D-78234 Engen-Welschingen Tel.: +49(0)7733-9487-0 Fax: +49(0)7733-9487-32

eMail: info@meder.com Internet: www.meder.com Headquarter USA MEDER electronic Inc. 766 Falmouth Rd Mashpee, MA 02649

Phone: +1/ 508-539-0002 Fax: +1/ 508-539-4088 eMail: <u>salesusa@meder.com</u> Reed Sensor: MK2/0-1A71-500W

Part Number: 2220711054



Switching Distance	Conditions at 20°C	Min.	Тур.	Max.	Units
Contact opened / Switch modified		5,5		13,5	mm
Contact closed / Switch modified		4,5		10	mm

Contact Data 71/7 (Form A/Dry)					
Contact Rating	Any combination of the switching voltage and current must not exceed the given rated power			10	W
Switching Voltage	DC or Peak AC			200	V
Switching Current	DC or Peak AC			0,5	Α
Carry Current	DC or Peak AC			1,75	Α
Static Contact Resistance (initial)	Measured with 40% overdrive			150	mΩ
Insulation Resistance	RH 45%	10 <sup>12</sup>			Ω
Breakdown Voltage		310			VDC
Operate Time, including Bounce	Measured with 40% overdrive			0,5	ms
Release Time				0,1	ms
Capacitance			0,2		pF

Environmental Data					
Shock	½ sine wave, duration 11ms			30	g
Vibration	from 10 - 2000 Hz			10	g
Operating Temperature	10°C/min max. allowable	-20		85	°C
Storage Temperature	10°C/min max. allowable	-35		85	°C
Material of Case		tereph	sfibre reinfor thalate (PBT inguishing V	P) self-éxting	juishing
Sealing Compound			Polyur	ethane	
Cable	Round cable LIYY 2 x 0,25 mm <sup>2</sup> , Ø3,4 mm, Ends of cable with a				wn / white)
Contact Resistance with Cable	Measured with 40% overdrive			230	mΩ

Pomarke	The switching distance can be decreased by mounting the MK2/0 on iron.
Remarks	When mounting the sensor, magnetically conductive screws must not be used.

Modifications in the sense of technical progress are reserved DESIGNED BY: APPROVED BY: APPROVED BY: DATE: 05.10.2000 PROVED BY: Werner Kovacs APPROVED BY: Theo Fritschi DATE: 08.12.2003