

Indenter with test diamond 136° Vickers

Type HV24, for stationary hardness testers

Application:

Indenter with test diamond 136° Vickers, for e.g. WOLPERT TESTOR/WPM/FRANK hardness testers

Art. no.	42215 600
Testing method	Vickers
Test body	Diamond pyramid 136°
Suitable for min. testing method	HV 5
Calibration certificate	DAkkS calibration certificate according to DIN EN ISO
Shank diameter	6.35 mm
Shaft length	12 mm
Functional diameter indenter	6 mm
Functional length indenter	17 mm
Offset functional diameter indenter	5 mm
Offset functional length indenter	6 mm
Length indenter	29 mm
Gross Weight	0.200 kg
Product Group	427

