

REVISION RECORD			
REV	ECN	DESCRIPTION	DRFT DATE

NOTES1:

UL Standard

1. Rated voltage/current : 300V / 15A
2. Withstanding voltage : AC1600V/1Min.
3. Torque value : M3 , 5.16Lb.in
4. Wire range : 28~12AWG

IEC Standard

1. Pollution degree	2
Overvoltage category	III
Rate impulse voltage(KV)	4.0KV
Rate voltage(V)	320V
Rate current(A)	20A

2. Torque value : M3 , 0.59N.m
3. Wire range : 1.0~2.5mm²





NOTES2:

1. Dimension shall be interpreted per ASME Y14.5-2009
2. Pitch : 5.08mm, Poles : N=02~xxP
3. Stripping length : 7~8mm
4. Operating temperature: -40°C~+105°C
5. Undimensioned tolerances:

Pitch	range	in mm	Nominal dimension	range	in mm	tolerance
Over	6	10	Over	30	60	Over
To	10	10	To	100	150	To
6	10	24	30	60	100	150
±0.15/±0.20/±0.30/±0.50/±0.70/±1.00/±1.30 ±2°						


6. RoHS Compliance

Clasp on the left from this view



2EDGK - 5.08 - XXP - 1Y - 1000A (H)

(Series No.)(Pitch)(Poles)(Single Pitch) (Color):1.(Grey) 2.(Blue) 3.(Black) 4.(Green) 5.(Orange) 6.(Red) 7.(Transparent) 8.(Yellow) 9.(White)



DETACHED LISTS			
PART NO.:	/	NAME:	DEGSON [®] NINGBO DEGSON ELECTRICAL CO., LTD 宁波高松电子有限公司
APPD:		TITLE:	2EDGK-5.08-XXP-1Y-1000A(H)
CHKD:		CUSTOMER DRAWING	REV DO-1
DRFT:	ZYP 2017.04.13	DRAWING NO.:	SHEET 1/1
THIRD ANGLE PROJECTION		DO NOT SCALE DRAWING	SCALE 1:1