

AMPERE TRAFFIC TAPE EXTRA

PRODUCT DESCRIPTION

Our general purpose PVC tape products are a great choice for floor aisle marking, warehouses and offices.

Inside use only. Durable Ampere TRAFFIC Floor Tape is providing good adhesive tack and flow, making it a good choice for most industrial applications.

Durable Ampere TRAFFIC Floor Tape must be applied on clean, dry, grease free and oil free surfaces.

Durable Ampere TRAFFIC Floor Tape should be stored at room temperature and kept from moisture and heat source.

Striped colorful appearance for maximum security

Color : striped yellow and black (dual color at 45°)
striped red and white (dual color at 45°)

Length : 33 m

Width : 50 mm / 75 mm

Safety note: Durable Ampere TRAFFIC Floor Tape have a smooth slick surface that will become particularly slippery when wet. Please take this into consideration when choosing this product for your intended application.

Before use, we recommend you to do a test to ensure that product is compatible with your support.

Property	Measurement	Test Method
PVC Film		
Thickness	0.2 mm	PSTC-33
Tensile Strength	> 5.75 N / mm	ASTM-D638
Elongation	> 200%	ASTM-D638
Rubber Adhesive	Vinyl with pressure sensitive adhesive	
Adhesion to steel	0.15 N / m	ASTM D-1000
Adhesion to backing	0.15 N / m	ASTM D-1000
Operational Temp.	-10°C to 60°C	
Min Application Temp.	10°C	

Nota : The information here described was obtained from sources which we believe are reliable. However the information is provided without any warranty, express or implied, regarding its correctness and they do not commit A.M.P.E.R.E system SAS company liability.