# Reflex Sensor with Background Suppression

HO08PA

Part Number




### • Adjustable switching distance

- Excellent ambient light suppression
- High switching frequency
- Large detection range

## **Technical Data**


Optical Data		
Range	80 mm	
Adjustable Range	2580 mm	
Switching Hysteresis	see Table 1	
Light Source	Red Light	
Service Life (T = +25 °C)	100000 h	
Max. Ambient Light	10000 Lux	
Light Spot Diameter	see Table 1	
Electrical Data		
Supply Voltage	1030 V DC	
Current Consumption (Ub = 24 V)	< 40 mA	
Switching Frequency	1 kHz	
Response Time	500 µs	
Temperature Drift	< 5 %	
Temperature Range	-2560 °C	
Switching Output Voltage Drop	< 2,5 V	
PNP Switching Output/Switching Current	200 mA	
Short Circuit Protection	yes	
Reverse Polarity Protection	yes	
Overload Protection	yes	
Protection Class	III	
Mechanical Data		
Setting Method	Potentiometer	
Housing Material	CuZn, nickel-plated	
Full Encapsulation	yes	
Degree of Protection	IP67	
Connection	Cable, 4-wire, 2 m	
PNP NO/NC antivalent		
Connection Diagram No.	201	
Control Panel No.	<b>O</b> 3	
Suitable Mounting Technology No.	170	

These sensors detect distance by measuring angles. They are particularly good at recognizing objects in front of any background. The color, shape and surface characteristics of the object have practically no influence on sensor switching performance. Also these sensors don't influence each other if their light spots are pointed onto the same spot or against each other.



**Photoelectronic Sensors** 





Т

Z S

RxD TxD

RDY Ready

GND

CL

E/A

e

PoF

IN

Teach Input Time Delay (activation)

Shielding Interface Receive Path

Interface Send Path

Output/Input progra

BLD+/- Ethernet Gigabit bidirect. data line (A-D) EN0rsez Encoder 0-pulse 0-0 (TTL)

Ground Clock

IO-Link

Power over Et

Safety Input

OSSD Safety Output

Signal Signal Output

#### Table 1

Awv

SY-

SnR

La

Mag RES

EDM

Synchronization

Receiver-Line

Emitter-Line

Rx+/- Ethernet Receive Path

Magnet activation

Input confirmation Contactor Monitoring

Tx+/- Ethernet Send Path

Ground for the Synchronization

Grounding Switching Distance Reduction

Interfaces-Bus A(+)/B(-) Emitted Light disengageable

Detection Range	40 mm	60 mm	80 mm
Light Spot Diameter	3 mm	5 mm	7 mm
Switching Hysteresis	< 2 mm	< 3 mm	< 8 mm

#### Switching Distance Deviation

Typical characteristic curve based on white, 90 % remission

Maintenance

Brown Red

Orange

Green

Blue

Violet

Grev

PK Pink GNYE Green/Yellow

rsv reserved Wire Colors according to DIN IEC 757

M rsv

BK Black

ΒN

RD

OG

YE

GN

BU

VT

GY

WΗ White

