



SIMATIC DP, 1 ELECTRON. MODULE FOR ET 200S, 8 DO DC24V/0,5A, 15 MM WIDTH, 1 PIECE PER PACKAGING UNIT

Figure similar

Supply voltage	
Reverse voltage protection	Yes
Load voltage L+	
<ul style="list-style-type: none"> <li>Rated value (DC)</li> </ul>	24 V
<ul style="list-style-type: none"> <li>Reverse polarity protection</li> </ul>	Yes
Input current	
from load voltage L+ (without load), max.	5 mA; Per channel
from backplane bus 3.3 V DC, max.	10 mA
Power losses	
Power loss, typ.	1.5 W
Address area	
Address space per module	
<ul style="list-style-type: none"> <li>without packing</li> </ul>	1 byte
Digital outputs	
Number of digital outputs	8
short-circuit protection	Yes
<ul style="list-style-type: none"> <li>Response threshold, typ.</li> </ul>	o.k.
Limitation of inductive shutdown voltage to	o.k.
Controlling a digital input	Yes
Switching capacity of the outputs	
<ul style="list-style-type: none"> <li>on lamp load, max.</li> </ul>	5 W
Load resistance range	
<ul style="list-style-type: none"> <li>lower limit</li> </ul>	48 $\Omega$

• upper limit	3 400 Ω
<b>Output voltage</b>	
• for signal "1", min.	o.k.
<b>Output current</b>	
• for signal "1" rated value	0.5 A
• for signal "1" permissible range for 0 to 60 °C, min.	7 mA
• for signal "1" permissible range for 0 to 60 °C, max.	600 mA
• for signal "0" residual current, max.	0.3 mA
<b>Output delay with resistive load</b>	
• "0" to "1", max.	300 μs
• "1" to "0", max.	600 μs
<b>Parallel switching of 2 outputs</b>	
• for increased power	No
• for redundant control of a load	Yes
<b>Switching frequency</b>	
• with resistive load, max.	100 Hz
• with inductive load, max.	2 Hz
• on lamp load, max.	10 Hz
<b>Aggregate current of outputs (per group)</b>	
all mounting positions	
— up to 60 °C, max.	4 A
<b>Cable length</b>	
• shielded, max.	1 000 m
• Unshielded, max.	600 m
<b>Isochronous mode</b>	
Isochronous operation (application synchronized up to terminal)	Yes; jitter incumbered < 100us
<b>Interrupts/diagnostics/status information</b>	
<b>Diagnostic messages</b>	
• Diagnostic functions	No
<b>Diagnostics indication LED</b>	
• Status indicator digital output (green)	Yes
<b>Parameter</b>	
Remark	3-byte parameter (not accessible for the user)
<b>Galvanic isolation</b>	
<b>Galvanic isolation digital outputs</b>	
• between the channels	No
• between the channels and the backplane bus	Yes

## Isolation

Isolation checked with	500 V DC
------------------------	----------

## Dimensions

Width	15 mm
-------	-------

Height	81 mm
--------	-------

Depth	52 mm
-------	-------

## Weights

Weight, approx.	40 g
-----------------	------

<b>last modified:</b>	12.03.2015
-----------------------	------------