

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0357480410](#)  
**Status:** **Active**  
**Overview:** [VersaBlade Wire-to-Wire Connector System](#)  
**Description:** [VersaBlade Female Crimp Terminal, 24 AWG, Type B](#)

**Documents:**

<a href="#">Drawing (PDF)</a>	<a href="#">Application Specification 351500000ASENG-000 (PDF)</a>
<a href="#">3D Model</a>	<a href="#">Application Specification 351500000ASKOR-000 (PDF)</a>
<a href="#">3D Model (PDF)</a>	<a href="#">Packaging Specification PK-35748-001-001 (PDF)</a>
<a href="#">Product Specification 351800400-001 (PDF)</a>	<a href="#">Datasheet (PDF)</a>
<a href="#">Product Specification 351800600-001 (PDF)</a>	<a href="#">Brochure (PDF)</a>
<a href="#">Product Specification PS-35150-003-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>

**General**

Product Family	Crimp Terminals
Series	35748
Application	Power, Wire-to-Wire
Crimp Quality Equipment	Yes
Overview	<a href="#">VersaBlade Wire-to-Wire Connector System</a>
Product Name	VersaBlade
Taxonomy	Crimp Terminals
UPC	756054339114

**Physical**

Durability (mating cycles max)	30
Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.240/g
Packaging Type	Reel
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.45mm max.
Wire Size AWG	24
Wire Size mm <sup>2</sup>	0.29

**Solder Process Data**

Lead-freeProcess Capability	N/A
-----------------------------	-----

**Material Info**

**Reference - Drawing Numbers**

Application Specification	351500000AS_ENG-000, 351500000AS_KOR-000
Crimp Specification	CS-35745-002-001
Packaging Specification	PK-35748-001-001
Product Specification	351800400-001, 351800600-001, PS-35150-003-001
Sales Drawing	SD-35748-001-001, SD-35748-003-001



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained per -  
D(2022)9120-DC (17  
Jan 2023)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

35748 Series

**Use With**

VersaBlade Standard Receptacle Housings  
[351500400](#) , [351500404](#) , [351500409](#) ,  
[351500410](#) , [351500412](#) , [351500414](#) ,  
[351500419](#) , [351503419](#) , [351504419](#) ,  
[351510310](#) , [351510314](#) , [351510319](#) ,  
[351513319](#) , [351514319](#) <br> VersaBlade  
Standard Plug Housings [351510410](#) ,  
[351510412](#) , [351510414](#) , [351510419](#) ,  
[351513419](#) , [351514419](#) , [351510610](#) ,  
[351510612](#) , [351510614](#) , [351510619](#) ,  
[351513619](#) , [351514619](#) <br>VersaBlade  
Multi-Module Receptacle Housings  
[351800400](#) , [351800404](#) , [351800409](#) ,  
[351803409](#) , [351804409](#) , [2041020429](#)  
<br>VersaBlade Multi-Module Plug  
Housings [351810220](#) , [359650220](#) ,  
[359650224](#) , [359659220](#) , [359659223](#) ,  
[359659224](#)

**Application Tooling** | [FAQ](#)

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

<b>Description</b>	<b>Product #</b>
--------------------	------------------

Extraction and	<u>638132700</u>
----------------	------------------

Activation Tool	
-----------------	--

Hand Crimp Tool for	<u>638196900</u>
---------------------	------------------

Industry standard	
-------------------	--

1.78mm Tab	
------------	--

Terminals, 24-26	
------------------	--

AWG Wire	
----------	--

FineAdjust Applicator	<u>639044200</u>
-----------------------	------------------

for .070 Male and	
-------------------	--

Female Crimp	
--------------	--

Terminals, 24 AWG	
-------------------	--

T2 Terminator	<u>639114300</u>
---------------	------------------

for .070 Female	
-----------------	--

Crimp Terminal	
----------------	--

This document was generated on 03/07/2023

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**