

# Kingbright

## PHOTOCOUPLER

### Features


- 1.AC inputs.
- 2.High current transfer ratio.
- 3.Opaque type, mini-flat package.
- 4.Subminiature type (The volume is smaller than that of our conventional DIP type by as far as 30%).
- 5.Isolation voltage between input and output  $V_{iso}:3750V_{rms}$ .
- 6.Emloys double transfer mold technology.
- 7.Recognized by UL and CUL, file NO.E225308.
- 8.Approved by VDE 0884 Teil2(NO:40017614).
- 9.Package : 1000Pcs / Reel.
- 10.Moisture sensitivity level : level 4.
- 11.RoHS Compliant.

### Applications


- 1.Hybrid substrates that require high density mounting.

### \*PACKAGE DIMENSIONS (UNIT:mm)

#### SMD Type



#### Internal connection diagram



#### Notes:

1. All dimensions are in millimeters (inches).
2. Tolerance is  $\pm 0.25(0.01)$  unless otherwise noted.
3. Lead spacing is measured where the leads emerge from the package.
4. The specifications, characteristics and technical data described in the data-sheet are subject to change without prior notice.



**Kingbright****PHOTOCOUPLER****\*Absolute Maximum Ratings (Ta=25°C)**

| Parameter                |                             | Symbol | Rating      | Unit |
|--------------------------|-----------------------------|--------|-------------|------|
| Input                    | Forward current             | IF     | ±50         | mA   |
|                          | Power dissipation           | P      | 70          | mW   |
| Output                   | Collector-emitter voltage   | VCEO   | 35          | V    |
|                          | Emitter-collector voltage   | VECO   | 6           | V    |
|                          | Collector current           | IC     | 50          | mA   |
|                          | Collector power dissipation | PC     | 150         | mW   |
| Total power dissipation  |                             | P tot  | 170         | mW   |
| *1 Isolation voltage     |                             | V iso  | 3750        | Vrms |
| Operating temperature    |                             | T opr  | -30 to +100 | °C   |
| Storage temperature      |                             | T stg  | -40 to +125 | °C   |
| *2 Soldering temperature |                             | T sol  | 260         | °C   |

\*1 40 to 60%RH, AC for 1 minute.

\*2 For 10 seconds.


\*3 Relative humidity levels maintained between 40% and 60% in production area are recommended to avoid the build-up of static electricity – Ref JEDEC/JESD625-A and JEDEC/J-STD-033.

**\*Electro-optical Characteristics**


| Parameter                |                                      | Symbol            | Conditions    | Min.                     | Typ. | Max.             | Unit |    |
|--------------------------|--------------------------------------|-------------------|---------------|--------------------------|------|------------------|------|----|
| Input                    | Forward voltage                      | VF                | IF=± 20mA     | -                        | 1.2  | 1.4              | V    |    |
|                          | Peak forward voltage                 | VFM               | IFM=0.5A      | -                        | -    | 3.0              | V    |    |
| Output                   | Collector dark current               | ICEO              | Vce=20V IF=0  | -                        | -    | 10 <sup>-7</sup> | A    |    |
|                          | Collector-emitter breakdown voltage  | BV <sub>CEO</sub> | IC=0.1mA IF=0 | 35                       | -    | -                | V    |    |
|                          | Emitter-collector breakdown voltage  | BV <sub>ECO</sub> | IE=10uA IF=0  | 6                        | -    | -                | V    |    |
| Transfer characteristics | Current transfer ration              |                   | CTR           | IF=± 1mA Vce=5V          | 20   | -                | 400  | %  |
|                          | Collector-emitter saturation voltage |                   | VCE (sat)     | IF=± 20mA IC=1mA         | -    | 0.1              | 0.2  | V  |
|                          | Response time                        | Rise time         | tr            | Vce=2V IC=2mA<br>RL=100Ω | -    | 4                | 18   | uS |
|                          |                                      | Fall time         | tf            |                          | -    | 3                | 18   | uS |

| Model No. | Rank mark | CTR(%)     |
|-----------|-----------|------------|
| KB354N1T  | A         | 50 to 150  |
| KB354NT   | L         | 20 to 50   |
|           | A         | 50 to 150  |
|           | B         | 150 to 300 |


**Fig. 1 Current Transfer vs. Forward Current**




**Fig. 2 Forward Current vs. Forward voltage**




**Fig. 3 Collector Current vs. Collector-emitter Voltage**




**Fig. 4 Forward Current vs. Ambient Temperature**




**Fig. 5 Collector-emitter Saturation Voltage vs. Ambient Temperature**




**Fig. 6 Response Time vs. Load Resistance**




**Test Circuit for Response Time**



**Fig. 7 Collector-emitter Saturation Voltage vs. Forward Current**




**Fig. 8 Collector Dark Current vs. Ambient Temperature**



**Kingbright****PHOTOCOUPLER****\*NOTES ON HANDLING****1.Cautions regarding noise**

Be aware that power is suddenly into the componment any surge current may cause damage happen, even if the voltage is within the absolute maximum ratings.

Reflow Soldering Profile For Lead-free SMT Process.

**NOTES:**

1. We recommend the reflow temperature 245°C(+/-5°C). The maximum soldering temperature should be limited to 260°C.
2. Don't cause stress to the epoxy resin while it is exposed to high temperature.
3. Number of reflow process shall be 2 times or less.

**CAUTION**

Within this device there exists GaAs (Gallium Arsenide) material which is a harmful substance if ingested. GaAs dust and fumes are toxic. Do not break, cut or pulverize the product, or use chemicals to dissolve them.


**RESTRICTIONS ON PRODUCT USE**

- The information in this document is subject to change without notice. Before using this document, please confirm that this is the latest version. Not all devices / types available in every country.
- We are mention about our product quality stability, semiconductor devices in general can malfunction or fail due to their inherent electrical sensitivity and vulnerability to physical stress. It is the responsibility of the buyer, when utilizing KINGBRIGHT products, to observe standards of safety, and to a avoid situations in which a malfunction or failure of a KINGBRIGHT product could cause loss of human life, bodily injury or damage to property. In developing your designs, please ensure that KINGBRIGHT products are used within specified operating ranges as set forth in the most recent products specifications.


# Kingbright

## PHOTOCOUPLER


### Outline and Dimension (Tape) (Units : mm)



Tape Direction



### Outline and Dimension (Reel)





Packing:1000pcs/reel


# Kingbright

## PHOTOCOUPLER

PACKING & LABEL SPECIFICATIONS

KB354NT



|  |  |
|--|--|
| <h1>Kingbright</h1>  |  |
| P/NO: KB354xxx   |  |
| QTY: 1000 pcs  | Q.C. <span style="border: 1px solid black; border-radius: 50%; padding: 2px;">QC<br/>XXXXXXX<br/>PASSED</span> |
| S/N: XXXX  |  |
| CODE: XXX  |  |
| LOT NO:  |  |
| <br>XXXXXXXXXX |  |
| RoHS Compliant   |  |