

Request Samples ()



Check Inventory (>)





FEATURES

- AEC-Q200 Qualified
- Shielded construction
- Soft saturation
- Low DCR per cubic mm
- Designed for switching frequencies between 100KHz-5MHz







ELECTRICAL SPECIFICATIONS @ 25°C

PART NUMBER*	INDUCTANCE	TOLERANCE	IRMS	ISAT	DC RESISTANCE (mΩ)		TYPE	
	(uH)	(%)	(A)	(A)	TYP	MAX		
AMDLA4020Q-R22MT	0.22	20	14	24	6.2	7.4	Lead Frame	
AMDLA4020Q-R33MT	0.33	20	11	14	7.0	8.4	Lead Frame	
AMDLA4020Q-R47MT	0.47	20	10	14	9.4	11.3	Lead Frame	
AMDLA4020Q-R68MT	0.68	20	9.0	12	13.3	16	Lead Frame	
AMDLA4020Q-1R0MT	1.0	20	6.5	9.0	16.4	20	Lead Frame	
AMDLA4020Q-1R5MT	1.5	20	4.8	7.5	22	26	Lead Frame	
AMDLA4020Q-2R2MT	2.2	20	4.5	6.0	31.5	38	Lead Frame	
AMDLA4020Q-3R3MT	3.3	20	3.5	5.0	45	54	Lead Frame	
AMDLA4020Q-4R7MT	4.7	20	3.0	4.5	58	70	Lead Frame	
AMDLA4020Q-6R8MT	6.8	20	2.4	3.5	86	103	Lead Frame	
AMDLA4020Q-100MT	10.0	20	2.0	3.5	170	190	Lead Frame	
AMDLA4020Q-150MT	15.0	20	1.8	2.6	240	275	Lead Frame	
AMDLA4020Q-220MT	22.0	20	1.2	2.1	265	320	Lead Frame	

^{*} Please refer to Part Identification section

Test Conditions

Inductance: 1 MHz, 1 V, 0 Adc Humidity Range: 65% RH

Temperature Rise Current: Current measured at Δ T of 40°C Saturation Current: Current measured at Δ L of 30%

GENERAL SPECIFICATIONS

Operating Temperature:

-55°C to +125°C with (40°C rise) Irms current.

Maximum Part Temperature: +125°C **Components Storage Temperature:**

-55°C to +125°C

Tape and Reel Packaging Temperature: -20°C to +65°C

MSL: Level 1

MATERIALS

Core: Metal Alloy Wire: Copper Terminal: Tin Plating Black Ink:

PART BUILDER




1. Tolerance: M = 20%


2. Packaging: B = Bulk

T = Tape and Reel (3,000pcs/reel)

PRODUCT DIMENSIONS



RECOMMENDED LANDING PATTERN






^{*}Refer to Electrical Specification table



RECOMMENDED REFLOW PROFILE



ZONE	DESCRIPTION	TEMPERATURE	TIMES		
1	Preheat	T _{smin} ~ T _{smax} 150°C ~ 180°C	60 ~ 120 sec.		
2	Reflow	T _∟ 230°C	30 ~ 40 sec.		
3	Peak Heat	T _P 250°C+0/-5°C	10 sec. MAX		






PACKAGING


Tape and Reel: 3,000 Units per Carton: 24,000

T&R per Carton: 8


Weight per Carton: 14.5 kg Weight per Unit: 0.43 g

Carton Dimensions: 360 x 360 x 400 mm





TYPE	Α	В	С	D
13" x 12 mm	12.4 +2/-0	100.0 ± 0.5	13.0 +0.5/-0.2	330.0



B _o	A_{o}	K _o	Р	W	F	T	D
4.85 ± 0.1	4.45 ± 0.1	2.3 ± 0.1	8.0 ± 0.1	12.0 ± 0.3	5.5 ± 0.1	0.3 ± 0.05	1.5

Dimensions: mm

This product is commercial off-the-shelf (COTS) and not specifically designed for automotive, military, aviation, aerospace, implantable, life-dependent medical or safety applications. This product is not recommended for use in any application requiring high reliability in which component failure could result in loss of life and/or property damage without prior written approval from Abracon. Specifications are subject to change without notice. Contact Abracon for more information.



Headquarters:

5101 Hidden Creek Ln Spicewood TX 78669 Phone: 512-371-6159 | Fax: 512-351-8858