



# VANSON ELECTRONICS LTD.

TEL: (852) 24271 741

19, FL., KINGSWAY INDUSTRIAL BLDG.,  
FLAT "H", 173-175 WO YI HOP RD.,  
KWAI CHUNG, N.T., KOWLOON,  
**HONG KONG**  
Email: sales@vanson.ws  
Fax: (852) 2480 5640

*Your Ref.*

*Our Ref.*

**Hong Kong**, May 31, 2017

Page: 1 of 3

## PRODUCT SPECIFICATIONS

|                |                                                      |
|----------------|------------------------------------------------------|
| Description:   | Switching Mode Regulated Adaptor                     |
| Model No.:     | SMP-30WME                                            |
| AC Plug:       | Direct plug in (EU plug)                             |
| Case color:    | Black                                                |
| Colour of LED: | Blue colour                                          |
| DC Plug:       | 5 ft. of cable with Detachable plugs                 |
| Connector tip: | With 7 detachable plugs (Part No. EP-7F)             |
| Dimensions:    | 85mm(L) x 50.5mm(W) x 50.5mm(H)(not including plugs) |
| Weight:        | 162 grams (not including plugs)                      |

## TECHNICAL SPECIFICATIONS

|                                                             |                                                                                             |
|-------------------------------------------------------------|---------------------------------------------------------------------------------------------|
| Primary Voltage and Frequency:                              | 100-240V AC 50/60Hz, 700mA                                                                  |
| Secondary voltage:<br>(Test method according to<br>EN60950) | 9V / 12V / 15V DC 1.5A $\pm$ 5%;<br>18V / 20V DC 1.2A $\pm$ 5%;<br>24V DC 1A $\pm$ 5%.      |
| Efficiency:                                                 | 78.5%                                                                                       |
| Ripple:                                                     | 130mV P-P max.                                                                              |
| Safety features:                                            | 1) Overload protection: Input power < 28W<br>2) Short circuit protection: Input power < 10W |
| Temperature                                                 | Storage temperature: -10°C to 55°C<br>Working temperature: 0°C to 35°C                      |



## VANSON ELECTRONICS LTD.

TEL: (852) 24271 741

19, FL., KINGSWAY INDUSTRIAL BLDG.,  
FLAT "H", 173-175 WO YI HOP RD.,  
KWAI CHUNG, N.T., KOWLOON,  
**HONG KONG**

Email: sales@vanson.ws

Fax: (852) 2480 5640


*Your Ref.*

*Our Ref.*

*Hong Kong, May 31, 2017*

Page: 2 of 3

### PRODUCT DRAWING:





# VANSON ELECTRONICS LTD.

TEL: (852) 24271 741

19, FL., KINGSWAY INDUSTRIAL BLDG.,  
FLAT "H", 173-175 WO YI HOP RD.,  
Kwai Chung, N.T., Kowloon,  
HONG KONG

Email: sales@vanson.ws  
Fax: (852) 2480 5640

Your Ref.

Our Ref.

Hong Kong, May 31, 2017

Page: 3 of 3

## PLUG DRAWING:

