

## SDQC offset steel boring bar, positive, right

for longitudinal and copy turning with DC indexable insert

**ATORN**<sup>®</sup>

### Application

For longitudinal and copy turning with DC 55° indexable insert.

### Version

- precision-manufactured steel boring bar, with inner cooling, offset, D type, 107.5° pitch angle, 55° tip angle, 7° clearance angle

### Advantage

- slim contour, optimised for copy turning work
- positive body geometry ensures low cutting forces



<b>Art. No.</b>	<b>17848 218</b>
<b>ISO name</b>	A 1216 M SDQC R/L 07
<b>Min. bore diameter</b>	19.5 mm
<b>Tapered diameter</b>	12 mm
<b>Shaft diameter</b>	16 mm
<b>Clearance length</b>	36 mm
<b>Length</b>	150 mm
<b>Clamping surface height</b>	15 mm
<b>Programming size</b>	11 mm
<b>Suitable for indexable inserts</b>	DC.. 0702..
<b>Tool design</b>	Right
<b>DIN</b>	8024

### EAN-Code

4050293347371