

Spacer sleeve for MK with clamping thread (DIN 6364)

ISO 12164 (DIN 69893)

ATORN[®]

Application

For holding tools with Morse taper shank in accordance with DIN 228 A with clamping thread.

Version

- Alloyed case-hardening steel, tensile strength in the core min. 950 N/mm²
- Case-hardened HRc 60 ± 2 (HV 700 ± 50), hardness depth 0.8 mm ± 0.2 mm, bronzed
- Taper angle tolerance quality < AT3 in accordance with DIN 7187 and DIN 2080
- max. concentricity < 0.005 mm



| | |
|----------------------------|------------------|
| Art. No. | 23163 017 |
| Mount, on tool side | MK 5 |
| Projecting length | 200 mm |
| Outer diameter | 63 mm |
| Tool holding device | HSK 100 |

EAN-Code

40502937 12872