

## TE Type K - Thermal pair with connector

flexible, PTFE design




### Application:

The temperature sensor with Teflon coating (PTFE) is suitable for quick and easy air temperature measurements. The flexible thermal wire can be routed through holes, gaps or door seals, for example.

### Execution:

- Sensor type: TE Type K
- Measuring range: -50 to +250 °C
- Class 2 in accordance with EN 60584-2
- Response time: 5 s
- Length/diameter of probe/sensor tube: 1500 mm/1.5 mm



<b>Art. no.</b>	<b>46108 205</b>
<b>Brand</b>	TESTO
<b>Manufacturer Part Number</b>	0602 0646
<b>Sensor type</b>	TE type K
<b>Probe type</b>	Thermocouples
<b>Min./max. temperature measuring range</b>	-50 to 250 °C
<b>Accuracy temperature</b>	Class 2 according to EN 60584-2
<b>Response time sensor</b>	5 s
<b>Diameter probe tube</b>	1.5 mm
<b>Length sensor tube</b>	1500 mm
<b>EN standard</b>	60584-1
<b>Gross Weight</b>	0.030 kg
<b>Product Group</b>	4CF

### EAN

4029547004476