



by   **MADE IN ITALY**

EXPLORERCASES by GTLine  
e-mail: sales@explorercases.com








## Cod. 3317.B



### TECHNICAL SPECIFICATIONS | SPECIFICHE TECNICHE

Internal dimensions Dimensioni interne	in. mm	12.99 330	9.21 234	6.69 170	2.68 68	4.02 102
External dimensions Dimensioni esterne	in. mm	14.17 360	11.97 304	7.64 194	- -	- -
Weight Empty Peso Vuota	lbs kg	5.05 2.29	Weight with Foam Peso con Spugna		lbs kg	5.53 2.51
Buoyancy Galleggiamento	lbs kg	15.43 7.0	Volume Volume		gallons litri	3.46 13.1
Temp. Rating Temp. Supportata	fahrenheit celsius	-27.4/210.2 -33/+99				

## FEATURES | CARATTERISTICHE

	<b>NEOSEAL 33</b> Neoprene seal
	<b>LABELCOVER 3317</b> PVC WATERPROOF I.D. LABEL Identification label (with protective cover)
	<b>PURGEVALVE.B</b> PURGEVALVE.B
	<b>FOAM .3317</b> FOAM KIT
	<b>REMOVABLE LID</b>
	<b>COUNTERBALANCE SUPPORTS</b>
	<b>Internal Slots</b> All cases are provided with internal slots for optional "panel mounting brackets" or "panel mounting rings"