
Vishay Semiconductors

Hyperfast Rectifier, 30 A FRED Pt[®]



30 A

650 V

1.6 V

27 ns

175 °C

TO-247AD 2L

Single

PRIMARY CHARACTERISTICS

I_{F(AV)}

 V_{R}

V_F at I_F

t_{rr} typ.

T_J max.

Package

Circuit configuration

www.vishay.com

- Low forward voltage drop
- Hyperfast soft recovery time
- 175 °C operating junction temperature
- Material categorization: for definitions of compliance please see <u>www.vishay.com/doc?99912</u>



RoHS COMPLIANT HALOGEN FREE

DESCRIPTION / APPLICATIONS

Hyperfast recovery rectifiers designed with optimized performance of forward voltage drop, hyperfast recovery time, and soft recovery.

The planar structure and the platinum doped life time control guarantee the best overall performance, ruggedness and reliability characteristics.

These devices are intended for use in PFC Boost stage in the AC/DC section of SMPS, inverters or as freewheeling diodes.

The extremely optimized stored charge and low recovery current minimize the switching losses and reduce over dissipation in the switching element and snubbers.

ABSOLUTE MAXIMUM RATINGS									
PARAMETER	SYMBOL	TEST CONDITIONS	MAX.	UNITS					
Repetitive peak reverse voltage	V _{RRM}		650	V					
Average rectified forward current	I _{F(AV)}	T _C = 111 °C	30	^					
Non-repetitive peak surge current	I _{FSM}	T_C = 25 °C, t_p = 8.3 ms, half sine wave	170	A					
Operating junction and storage temperatures	T _J , T _{Stg}		-55 to +175	°C					

ELECTRICAL SPECIFICATIONS (T_J = 25 °C unless otherwise specified)								
PARAMETER	SYMBOL	TEST CONDITIONS	MIN.	TYP.	MAX.	UNITS		
Breakdown voltage, blocking voltage	V _{BR} , V _R	I _R = 100 μA	650	-	-			
Forward voltage	V _F	I _F = 30 A	-	2.1	2.5	V		
		I _F = 30 A, T _J = 150 °C	-	1.6	1.7			
Reverse leakage current	I _R	$V_{R} = V_{R}$ rated	-	0.02	30			
neverse leakage current		$T_J = 150 \text{ °C}, V_R = V_R \text{ rated}$	-	-	300	μA		
Junction capacitance	CT	V _R = 650 V	-	22	-	pF		
Series inductance	L _S	Measured lead to lead 5 mm from package body	-	8.0	-	nH		

 Revision: 11-Jun-2018
 1
 Document Number: 96449

 For technical questions within your region: DiodesAmericas@vishay.com, DiodesAsia@vishay.com, DiodesEurope@vishay.com
 DiodesEurope@vishay.com

 THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000



www.vishay.com


Vishay Semiconductors

DYNAMIC RECOVERY CHARACTERISTICS ($T_J = 25$ °C unless otherwise specified)									
PARAMETER	SYMBOL	TEST CO	ONDITIONS	MIN.	TYP.	MAX.	UNITS		
Reverse recovery time	t _{rr}	$I_F = 1 \text{ A}, \ dI_F/dt = 100$	-	35	-				
		T _J = 25 °C		-	27	-	ns		
		T _J = 125 °C	l _F = 30 A dl _F /dt = 1000 A/μs V _R = 400 V	-	88	-			
Peak recovery current	I _{RRM}	T _J = 25 °C		-	15	-	A		
		T _J = 125 °C		-	24	-			
Reverse recovery charge	Q _{rr}	T _J = 25 °C		-	330	-			
		T _J = 125 °C		-	1350	-	110		

THERMAL - MECHANICAL SPECIFICATIONS									
PARAMETER	SYMBOL	TEST CONDITIONS	MIN.	TYP.	MAX.	UNITS			
Maximum junction and storage temperature range	T _J , T _{Stg}		-55	-	175	°C			
Thermal resistance, junction to case	R _{thJC}		-	0.7	1.1	°C/W			
Thermal resistance, case to heatsink	R _{thCS}	Mounting surface, flat, smooth, and greased	-	0.5	-				
Weight			-	5.5	-	g			
weight			-	0.2	-	oz.			
Mounting torque			1.2 (10)	-	2.4 (20)	kgf · cm (lbf · in)			
Marking device		Case style TO-247 2L		EPX3	8007L				





Vishay Semiconductors




www.vishay.com

ISHAY










Fig. 3 - Typical Junction Capacitance vs. Reverse Voltage





Fig. 4 - Maximum Thermal Impedance Z_{thJC} Characteristics



°C

1000

1000




Fig. 9 - Reverse Recovery Waveform and Definitions


extrapolated to zero current.

Revision: 11-Jun-2018	4	Document Number: 96449
For technical questions within your region:	DiodesAmericas@vishay.com, DiodesAsia@vishay.c	<u>:om, DiodesEurope@vishay.com</u>
	E WITHOUT NOTICE. THE PRODUCTS DESCRIBED CIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.co</u>	





ORDERING INFORMATION TABLE



ORDERING INFORMATION (Example)								
PREFERRED P/N QUANTITY PER TUBE MINIMUM ORDER QUANTITY PACKAGING DESCRIPTI								
VS-EPX3007L-N3	25	500	Antistatic plastic tube					

LINKS TO RELATED DOCUMENTS						
Dimensions www.vishay.com/doc?95536						
Part marking information	www.vishay.com/doc?95648					



Vishay Semiconductors

TO-247AD 2L

DIMENSIONS in millimeters and inches



Section C - C, D - D

(b, b2)

(4)

View	<u>/ B</u>

SYMBOL	MILLIN	MILLIMETERS		INCHES		NOTES	SYMBOL	MILLIMETERS		INCHES		NOTES
STIVIDUL	MIN.	MAX.	MIN.	MAX.	NOTES		STMDUL	MIN.	MAX.	MIN.	MAX.	NOTES
А	4.65	5.31	0.183	0.209			E	15.29	15.87	0.602	0.625	3
A1	2.21	2.59	0.087	0.102			E1	13.46	-	0.53	-	
A2	1.50	2.49	0.059	0.098			е	5.46	BSC	0.215	5 BSC	
b	0.99	1.40	0.039	0.055			ØК	0.2	254	0.0	010	
b1	0.99	1.35	0.039	0.053			L	19.81	20.32	0.780	0.800	
b2	1.65	2.39	0.065	0.094			L1	3.71	4.29	0.146	0.169	
b3	1.65	2.34	0.065	0.092			ØР	3.56	3.66	0.14	0.144	
С	0.38	0.89	0.015	0.035			Ø P1	-	6.98	-	0.275	
c1	0.38	0.84	0.015	0.033			Q	5.31	5.69	0.209	0.224	
D	19.71	20.70	0.776	0.815	3		R	4.52	5.49	0.178	0.216	
D1	13.08	-	0.515	-	4		S	5.51	BSC	0.217	' BSC	
D2	0.51	1.35	0.020	0.053				•		•		•

Notes

⁽¹⁾ Dimensioning and tolerancing per ASME Y14.5M-1994

(2) Contour of slot optional

(3) Dimension D and E do not include mold flash. These dimensions are measured at the outermost extremes of the plastic body

(4) Thermal pad contour optional with dimensions D1 and E1

(5) Lead finish uncontrolled in L1

⁽⁶⁾ Ø P to have a maximum draft angle of 1.5 to the top of the part with a maximum hole diameter of 3.91 mm (0.154")

⁽⁷⁾ Outline conforms to JEDEC[®] outline TO-247 with exception of dimension A min., D, E min., Q min., S, and note 4

Revision: 28-May-2018 Document Number: 95536 1 For technical questions within your region: DiodesAmericas@vishay.com, DiodesAsia@vishay.com, DiodesEurope@vishay.com THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishav.com/doc?91000



Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.