


- Up to **15 W** switching
- Highest quality instrumentation grade switches
- Sputtered ruthenium switches rated at **10 W, 0.5 A** or **15 W, 1.0 A**
- Plastic package with internal mu-metal magnetic screen
- Take up minimum board area of only **0.2 x 0.33** Inches; conserving PCB space
- Insulation resistance **>10<sup>12</sup> Ω**
- **3V** or **5V** coils with with a resistance **up to 2200 Ω** and optional internal diode
- **Additional build options are available**
- Many benefits compared to industry standard relays **(see last page)**
- Very sensitive relays ideal for portable equipment or other applications where low power consumption is required



Two switch types are available. Switch type number 1 is better suited for general purpose applications. Switch type 2 is better suited to low level or 'cold' switching.

These relays feature internal mu-metal magnetic screens. Mu-metal has the advantage of a high permeability and low magnetic remanence and eliminates problems that would otherwise occur due to magnetic interaction. Relays of this size without magnetic screening would be totally unsuitable for applications where dense packing is required. To learn more visit: [pickeringrelay.com/magnetic-interaction](http://pickeringrelay.com/magnetic-interaction)

### Switch Ratings - Dry Switches

| 1 Form A (energize to make) |
|-----------------------------|
| 15 W at 200 V               |
| 10 W at 200 V               |

### Series 118 switch ratings - contact ratings for each switch type

| Switch No | Switch form | Power rating | Max. switch current | Max. carry current | Max. switching volts | Life expectancy ops typical (see Note <sup>1</sup> ) | Operate time inc bounce (max) | Release time | Special features |
|-----------|-------------|--------------|---------------------|--------------------|----------------------|--|-------------------------------|--------------|------------------|
| 1         | A           | 15W          | 1.0A                | 1.2A               | 200                  | 10 <sup>9</sup>                                      | 0.6 ms                        | 0.35 ms      | General purpose  |
| 2         | A           | 10W          | 0.5A                | 1.2A               | 200                  | 10 <sup>9</sup>                                      | 0.6 ms                        | 0.35 ms      | Low level        |

#### Note<sup>1</sup>: Life Expectancy

The life of a reed relay depends upon the switch load and end of life criteria. For example, for an 'end of life' contact resistance specification of 1 Ω, switching low loads (10 V at 10 mA resistive) or when 'cold' switching, typical life is approx 1 x 10<sup>9</sup> ops. At the maximum load (resistive), typical life is 1 x 10<sup>7</sup> ops. In the event of abusive conditions, e.g. high currents due to capacitive inrushes, this figure reduces considerably. Pickering will be pleased to perform life testing with any particular load condition.

### Operating Voltages

| Coil voltage - nominal | Must operate voltage - maximum at 25°C | Must release voltage - minimum at 25°C |
|------------------------|--|--|
| 3 V                    | 2.25 V                                 | 0.3 V                                  |
| 5 V                    | 3.75 V                                 | 0.5 V                                  |

### Environmental Specification/Mechanical Characteristics

In the table below, the upper temperature limit can be extended to +125 °C if the coil drive voltage is increased to accommodate the resistance/temperature coefficient of the copper coil winding. This is approximately 0.4% per °C. This means that at 125 °C the coil drive voltage will need to be increased by approximately  $40 \times 0.4 = 16\%$  to maintain the required magnetic drive level. Please contact [sales@pickeringrelay.com](mailto:sales@pickeringrelay.com) for assistance.

|  |                   |
|--|-------------------|
| Operating Temperature Range                        | -20 °C to +85 °C  |
| Storage Temperature Range                          | -35 °C to +100 °C |
| Shock Resistance                                   | 50 g              |
| Vibration Resistance (10 - 2000 Hz)                | 20 g              |
| Soldering Temperature (max) (10 s max)             | 270 °C            |
| Washability (Proper drying process is recommended) | Fully Sealed      |

### Dry Relay: Series 118 Coil data and type numbers

| Device Type                                | Type Number  | Coil (V) | Coil resistance | Max. contact resistance (initial) | Insulation resistance (minimum at 25 °C) (see Note <sup>4</sup> ) |                    | Capacitance (typical) (see Note <sup>2,3</sup> ) |                    |
|--|--------------|----------|-----------------|-----------------------------------|---|--------------------|--|--------------------|
|  |              |          |                 |                                   | Switch to coil  | Across switch      | Closed switch to coil                            | Across open switch |
| 1 Form A<br>Switch No. 1<br>Package Type 1 | 118-1-A-5/1D | 5        | 1500 Ω          | 0.12 Ω                            | 10 <sup>12</sup> Ω  | 10 <sup>12</sup> Ω | 3.0 pF   | 0.14 pF            |
| 1 Form A<br>Switch No. 2<br>Package Type 1 | 118-1-A-3/2D | 3        | 1000 Ω          | 0.12 Ω                            | 10 <sup>12</sup> Ω  | 10 <sup>12</sup> Ω | 3.0 pF   | 0.14 pF            |
|  | 118-1-A-5/2D | 5        | 2200 Ω          |                                   |   |                    |  |                    |

When an internal diode is required, the suffix D is added to the part number as shown in the table.

#### Note<sup>2</sup>: Switch to coil capacitance

Due to the asymmetrical internal construction of the relay, the capacitance to the coil from one switch connection is approximately half the capacitance of the other switch connection, pin 3 is lower. In some applications this feature may be used to advantage for example, in a multiplexer where it is desirable to minimize the capacitance of the common connection to maximize bandwidth.

#### Note<sup>3</sup>: Capacitance across open switch

The capacitance across the open switch was measured with other connections guarded.

#### Note<sup>4</sup>: Insulation resistance


Insulation resistance will reduce at higher temperatures. For more information on temperature effects [click here](#), or [contact Pickering](#) for more in depth guidance.

The technical information shown in this data sheet could contain inaccuracies or typographical errors. This information may be periodically changed or updated and these changes will be included in future versions of this data sheet.

For different values, latest specifications and product details, please contact your local Pickering sales office.

For **FREE** evaluation samples go to: [pickeringrelay.com/samples](http://pickeringrelay.com/samples)

### Pin Configuration, Weights and Dimensional Data (dimensions in inches, millimeters in brackets)



**Important:** Where the optional internal diode is fitted the correct coil polarity must be observed, as shown by the + symbol on the schematics. Pin 1 is the positive connection.

### Similar Relays Comparison

The Series 118 is unique in the Pickering range of reed relays. Pickering do not manufacture another series of relays with similar characteristics.

### Reed Relay Selection Tool

Because Pickering offer the largest range of high-quality reed relays, sometimes it can be difficult to find the right reed relay you require. That is why we created the Reed Relay Selector, this tool will help you narrow down our offering to get you the correct reed relay for your application. To try the tool today go to: [pickeringrelay.com/reed-relay-selector-tool](https://pickeringrelay.com/reed-relay-selector-tool)

### Standard Build Options

The Series 118 Reed Relays are available with a number of standard build options to tailor them to your specific application. These options are detailed in the table below. If you decide to go ahead and specify one, or more, of these options you will be allocated a unique part number suffix.


| Mechanical Build Options                              | Electrical Build Options                                       |
|---|--|
| Special pin configurations or pin lengths             | Different coil resistance                                      |
| Special print with customer's own part number or logo | Operate or de-operate time                                     |
| Custom packaging possibility                          | Pulse capability   |
|   | Enhanced specifications  |
|   | Non-standard coil voltages and resistance figures              |
|   | Special Life testing under customer's specific load conditions |
|   | Specific environmental requirements                            |
|   | Controlled thermal EMF possibility                             |

### Customization

If your specific requirements are not met by standard relay, or any of the standard build options, please speak to us to discuss producing a customized reed relay to service your specific application: [pickeringrelay.com/contact](http://pickeringrelay.com/contact)

### 3D Models

Interactive 3D models of the complete range of Pickering relay products in STEP, IGS and SLDPRN formats can be downloaded from the website: [pickeringrelay.com/3d-models](http://pickeringrelay.com/3d-models)



### Help

If you need any technical advice or other help, please do not hesitate to contact our Technical Sales Department. We will always be pleased to discuss Pickering relays with you. email: [techsales@pickeringrelay.com](mailto:techsales@pickeringrelay.com)

### Contact Us

UK Headquarters - email: [sales@pickeringrelay.com](mailto:sales@pickeringrelay.com) | Tel. +44 1255 428141

USA - email: [ussales@pickeringrelay.com](mailto:ussales@pickeringrelay.com) | Tel. +1 781 897 1710

Germany - email: [desales@pickeringtest.com](mailto:desales@pickeringtest.com) | Tel. +49 89 125 953 160

France - email: [frsales@pickeringtest.com](mailto:frsales@pickeringtest.com) | Tel. +33 9 72 58 77 00

Nordic - email: [ndsales@pickeringtest.com](mailto:ndsales@pickeringtest.com) | Tel. +46 340 69 06 69














Czech Republic: [czsales@pickeringtest.com](mailto:czsales@pickeringtest.com) | Tel. +420 558-987-613

China - email: [chinasales@pickeringtest.com](mailto:chinasales@pickeringtest.com) | Tel. +86 4008 799 765

For a full list of agents, distributors and representatives visit: [pickeringrelay.com/agents](http://pickeringrelay.com/agents)



# 10 Key Benefits of Pickering Reed Relays

| Key Benefit   | Pickering Reed Relays   | Typical Industry Reed Relays   |  |
|---|---|--|--|
| <b>1</b><br>Instrumentation Grade Reed Switches             | Instrumentation Grade Reed Switches with vacuum sputtered Ruthenium plating to ensure stable, long life up to 5x10E9 operations.  | Often low grade Reed Switches with electroplated Rhodium plating resulting in higher, less stable contact resistance.  |   |
| <b>2</b><br>Formerless Coil Construction                    | Formerless coil construction increases the coil winding volume, maximizing magnetic efficiency, allowing the use of less sensitive reed switches resulting in optimal switching action and extended lifetime at operational extremes.                     | Use of bobbins decreases the coil winding volume, resulting in having less magnetic drive and a need to use more sensitive reed switches which are inherently less stable with greatly reduced restoring forces.   |  <br>Pickering former-less coil      Typical industry coil wound on bobbin   |
| <b>3</b><br>Magnetic Screening                              | Mu-metal magnetic screening (either external or internal), enables ultra-high PCB side-by-side packing densities with minimal magnetic interaction, saving significant cost and space. <b>Pickering Mu-Metal magnetic screen - interaction approx. 5%</b> | Lower cost reed relays have minimal or no magnetic screening, resulting in magnetic interaction issues causing changes in operating and release voltages, timing and contact resistance, causing switches to not operate at their nominal voltages. <b>Typical industry screen - interaction approx. 30%</b> |  <br>X-Ray of Pickering mu-metal magnetic screen      X-Ray of typical industry magnetic screen  |
| <b>4</b><br>SoftCenter™ Technology                          | <b>SoftCenter™</b> technology, provides maximum cushioned protection of the reed switch, minimising internal lifetime stresses and extending the working life and contact stability.  | Transfer moulded reed relays (produced using high temperature/pressure), result in significant stresses to the glass reed switch which can cause the switch blades to deflect or misalign leading to changes in the operating characteristics, contact resistance stability and operating lifetime.          |  <br>Pickering soft center protection of the reed switch      Typical industry thermo-setting hard moulded protection of the reed switch |
| <b>5</b><br>100% Dynamic Testing                            | 100% testing for all operating parameters including dynamic contact wave-shape analysis with full data scrutiny to maintain consistency.  | Simple dc testing or just batch testing which may result in non-operational devices being supplied.  | <b>Dynamic Contact Resistance Test</b><br>   |
| <b>6</b><br>100% Inspection at Every Stage of Manufacturing | Inspection at every stage of manufacturing maintaining high levels of quality.  | Often limited batch inspection.  |   |
| <b>7</b><br>100% Thermal Cycling                            | Stress testing of the manufacturing processes, from -20°C to +85°C to -20°C, repeated 3 times.  | Rarely included resulting in field failures.   |   |
| <b>8</b><br>Flexible Manufacturing Process                  | Flexible manufacturing processes allow quick-turn manufacturing of small batches.   | Mass production: Usually large batch sizes and with no quick-turn manufacturing.   |   |
| <b>9</b><br>Custom Reed Relays                              | Our reed relays can be customized easily, e.g. special pin configurations, enhanced specifications, non-standard coil or resistance figures, special life testing, low capacitance, and more.   | Limited ability to customize.  |   |
| <b>10</b><br>Product Longevity                              | Pickering are committed to product longevity; our reed relays are manufactured and supported for more than 25 years from introduction, typically much longer.   | Most other manufacturers discontinue parts when they reach a low sales threshold; costing purchasing and R&D a great deal of unnecessary time and money to redesign and maintain supply.   |   |

For more information go to: [pickeringrelay.com/10-key-benefits](http://pickeringrelay.com/10-key-benefits)