



SITOP PSE200U SELECTIVITY MODULE 10A  
 SITOP PSE200U 10 A SELECTIVITY MODULE 4 CHANNELS  
 INPUT: 24 V DC OUTPUT: 24V DC/10 A PER CHANNEL OUTPUT  
 CURRENT ADJUSTABLE 3-10 WITH STATUS MESSAGE PER  
 CHANNEL

Input	
Type of the power supply network	Controlled DC voltage
Supply voltage / for DC / Rated value	24 V
Input voltage / for DC	22 ... 30
Oversoltage overload capability	35 V
Input current / at rated input voltage 24 V / Rated value	40 A
Output	
Voltage curve / at output	controlled DC voltage
Formula for output voltage	$V_{in} - \text{approx. } 0.2 \text{ V}$
Relative overall tolerance / of the voltage / Note	In accordance with the supplying input voltage
Number of outputs	4
Output current / up to 60 °C / per output / Rated value	10 A
Adjustable response value current / of the current-dependent overload release	3 ... 10
Type of response value setting	via potentiometer
Product property / parallel switching of outputs	No
Type of outputs connection	Simultaneous connection of all channels after power up of the supply voltage > 20 V, delay time of 25 ms, 100 ms or adjustable "load optimised" via DIP switch for sequential connection
Efficiency	
Efficiency in percent	99 %
Active power loss / at rated output current / at rated output current / typical	10 W

Switch-off characteristic per output	
Switching characteristic <ul style="list-style-type: none"> <li>• of the excess current</li> <li>• of the current limitation</li> <li>• of the immediate switch-off</li> </ul>	$I_{out} = 1.0 \dots 1.5 \times \text{set value}$ , switch-off after approx. 5 s $I_{out} = 1.5 \times \text{set value}$ , switch-off not before typ. 100 ms $I_{out} > \text{set value}$ and $V_{in} < 20 \text{ V}$ , switch-off after approx. 0.5 ms
Design of the reset device/resetting mechanism	via sensor per output
Remote reset function	Non-electrically isolated 24 V input (signal level "high" at $> 15 \text{ V}$ )

Protection and monitoring	
Overload protection type / for cables	15 A per output (not accessible)
Display version / for normal operation	Three-color LED per output: green LED for "Output switched through"; yellow LED for "Output switched off manually"; red LED for "Output switched off due to overcurrent"
Design of the switching contact / for signaling function	Status signal output (pulse/pause signal, can be evaluated via Simatic function block)

Safety	
Galvanic isolation / between input and output at switch-off	No
Operating resource protection class	Class III
Certificate of suitability <ul style="list-style-type: none"> <li>• CE marking</li> <li>• UL approval</li> <li>• as approval for USA</li> </ul>	Yes Yes UL-Recognized (UL 2367) File E328600; cULus-Listed (UL 508, CSA C22.2 No. 107.1) File E197259
Standard <ul style="list-style-type: none"> <li>• for safety</li> <li>• for explosion protection</li> </ul>	according to EN 60950-1 and EN 50178 IECEX (IEC 60079-0, -15); ATEX (EN 60079-0, -15); cCSAus (CSA C22.2 No. 213, No. 60079, ANSI/ISA 12.12.01, UL 60079)
Certificate of suitability <ul style="list-style-type: none"> <li>• relating to ATEX</li> <li>• Shipbuilding approval</li> </ul>	IECEX Ex nA IIC T4 Gc; ATEX (EX) II 3G Ex nA IIC T4 Gc; cCSAus Class I, Div. 2, Group ABCD, T4 Yes
Shipbuilding approval	GL, ABS
Protection class IP	IP20

EMC	
Standard <ul style="list-style-type: none"> <li>• for emitted interference</li> <li>• for interference immunity</li> </ul>	EN 55022 Class B EN 61000-6-2

Operating data	
Ambient temperature <ul style="list-style-type: none"> <li>• during operation</li> <li>— Note</li> <li>• during transport</li> </ul>	0 ... 60 with natural convection -40 ... +85

- during storage

-40 ... +85

## Mechanics

Type of electrical connection	screw-type terminals
<ul style="list-style-type: none"> <li>• at input</li> </ul>	+24 V: 2 screw terminals for 0.5 ... 10 mm <sup>2</sup> ; 0 V: 2 screw terminals for 0.5 ... 4 mm <sup>2</sup>
<ul style="list-style-type: none"> <li>• at output</li> </ul>	Output 1 ... 4: 1 screw terminal each for 0.5 ... 4 mm <sup>2</sup>
<ul style="list-style-type: none"> <li>• for signaling contact</li> </ul>	3 screw terminals for 0.5 ... 4 mm <sup>2</sup>
<ul style="list-style-type: none"> <li>• for auxiliary contacts</li> </ul>	Remote reset: 1 screw terminal for 0.5 ... 4 mm <sup>2</sup>
Width / of the enclosure	72 mm
Height / of the enclosure	80 mm
Depth / of the enclosure	72 mm
Installation width	72 mm
Mounting height	180 mm
Net weight	0.2 kg
Mounting type	Snaps onto DIN rail EN 60715 35x7.5/15
Mechanical accessories	Device identification label 20 mm × 7 mm, pastel-turquoise 3RT1900-1SB20
Other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)