

## SVUB boring bar, steel positive

for longitudinal and copy turning with VB indexable insert

**ATORN**<sup>®</sup>

### Application


for longitudinal and copy turning with VB indexable insert, 35°

### Version

- Precision-made boring bar, **steel**, with internal cooling, type V, attack angle 93°, tip angle 35°, clearance angle 5°

### Advantage

- very slim geometry, optimised for contour turning work
- positive body geometry ensures low cutting forces



<b>Art. No.</b>	<b>17855 112</b>
<b>ISO name</b>	A20R SVUB R/L 11
<b>Min. bore diameter</b>	24 mm
<b>Shaft diameter</b>	20 mm
<b>Clearance length</b>	20.5 mm
<b>Length</b>	200 mm
<b>Clamping surface height</b>	18 mm
<b>Suitable for indexable inserts</b>	VB.. 1103..
<b>Tool design</b>	Right

### EAN-Code

4050293562484