

## Collet chucks type ER25 in accordance with DIN 6499 A

UP = ultra precision, concentricity < 2 µm

**ATORN**<sup>®</sup>

### Application

For use on precision collet chucks

### Advantage

- Higher concentricity extends tool life

<b>Art. No.</b>	<b>23388 192</b>
<b>Collet type</b>	ER 25
<b>Clamping diameter</b>	12 mm
<b>Min./max. clamping range</b>	1-16 mm
<b>Outer diameter</b>	26 mm
<b>Length</b>	34 mm
<b>Clamping bypass</b>	-0.5 mm



### EAN-Code

4050293631463