
Vinyl-Insulated (Easy Entry) Spade Terminals







RoHS Compliant

Specifications:

Max. Electric Current : AWG | 22 | 20 | 18 | 16 | 14 | 12 | 10 |
Amperes | 9 | 12 | 17 | 18 | 30 | 35 | 50

Type : Spade
Termination Method : Crimp
Contact Plating : Tin
Insulator Material : Nylon
Max. Electrical Rating : 105°C 600V
Terminal Material : Copper

Dimensions							Part		
d2	W	F	L	E	D	d1	Т	Number	
0.126 (3.2)	0.224 (5.7)		0.874 (22.2)	0.441 (11.2)	0.157 (4)	0.067 (1.7)	0.03 (0.75)	MC29608	
0.146 (3.7)	0.252 (6.4)							MC29610	
								MC29616	
	0.283 (7.2)							MC29623	
0.169 (4.3)								MC29612	
								MC29625	
	0.319 (8.1)							MC29617	
0.209 (5.3)								MC29614	
								MC29627	
	0.374 (9.5)							MC29618	
0.146 (3.7)	0.236 (6)	0.256 (6.5)	0.886 (22.5)	0.453 (11.5)	0.177 (4.5)	0.091 (2.3)	0.031 (0.8)	MC29611	
0.146 (3.7)	0.236 (6)							MC29619	
	0.283 (7.2)							MC29624	
0.169 (4.3)		0.283 (7.2)							MC29613

Dimensions: Inches (Millimetres)

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro



Vinyl-Insulated (Easy Entry) Spade Terminals



Dimensions								Part
d2	W	F	L	E	D	d1	Т	Number
0.169 (4.3)	0.283 (7.2)							MC29626
								MC29620
	0.311 (7.9)	0.256 (6.5)	0.886 (22.5)	0.453 (11.5)	0.177 (4.5)	0.091 (2.3)	0.031 (0.8)	MC29615
								MC29628
	0.366 (9.3)							MC29621
0.169 (4.3)	0.254 (0)	0.276 (7)	1.047 (26.6)	0.555 (14.1)	0.248 (6.3)	0.134 (3.4)	0.039 (1)	MC29622
0.209 (5.3)	0.354 (9)							MC29609

Part Number Table

Description	Wire Range AWG mm ²	Stud Size	Colour	Part Number
		#4		MC29608
				MC29610
		#6		MC29616
	22-16 AWG 0.5-1.5 mm ²		Red	MC29623
		#8		MC29612
				MC29625
				MC29617
		#10		MC29614
				MC29627
				MC29618
Terminal, Spade / Fork, Crimp	16-14 AWG 1.5-2.5 mm ²	#6		MC29611
			Blue	MC29619
				MC29624
		#8		MC29613
				MC29626
				MC29620
		#10		MC29615
				MC29628
				MC29621
	12-10 AWG	#6	Yellow	MC29622
	4-6 mm ²	#10	I GIIOW	MC29609

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

