

Drawer cabinet system 550 S with 10 SOFT-CLOSE drawers

Depth 550 mm, width 722 mm

Application:

Particularly suitable for careful storage of delicate, sensitive tools and parts in drawers.

Execution:

- Solidly welded steel sheet construction
- Tilt-proof due to built-in individual drawer pull-out locking
- The drawers have high-quality Delrin rollers which means that they run quietly
- Drawers with slots all around for inserting compartment rails and dividers
- Perforated steel sheet base (25 mm hole spacing) for fastening and fixing components
- Aluminium grip handles with paper and cellophane strips and lateral cover caps

Advantage:

- The damping system brakes the drawer while closing; it closes the drawer smoothly and soundlessly by means of the self-closing mechanism
- Impact load on tools and parts stored in the drawer is reduced to a minimum due to the smooth-closing drawers
- High quality - made in Germany

FH mm	KH mm
90	70
90	70
90	70
90	70
90	70
90	70
90	70
90	70
90	70
120	100
120	100



Art. no.	50295 762
Brand	HK
Manufacturer Part Number	50295762
Number of drawers	10 PCS
With doors	No
Height	1036 mm
Width	722 mm
Depth	550 mm
Height x width x depth	1036 x 722 x 550 mm
Drawer width (inner dimension) x drawer depth (inner dimension)	600 x 450 mm
Drawer with slots	Yes
Perforated drawer base	Yes
Load-carrying capacity per drawer	100 kg
Drawer surface	0.27 m ²
Pullout type	Full extension
With SOFT-CLOSE closing function	Yes
With single pull-out safety brake	Yes
Central locking	Yes
Material of cover panel	Wood, plastic-coated
Cabinet colour	Optional
Colour of front	Optional
Surface	Powder-coated
Functions	RFID possible
Model	S5 32/10
Overall surface	2.7 m ²
Lock type	DOM® locking system
Material	Sheet steel
Gross Weight	154.000 kg
Product Group	5BB

EAN

405362504972 1