

Carbide milling bits with INOX steel teeth (with teeth in accordance with DIN 8033)

Shank diameter 6 mm



Application:

Deburring, machining contours, chamfering/rounding edges, milling out for preparation of deposit welds, preparation/levelling of welding seams, cleaning cast metal, changing geometries.

Advantage:

- Extremely high cutting performance on all austenitic, rust and acid-resistant steels, stainless steel (INOX)
- Significantly reduced vibration and less noise



Art. no.	76007 310
Brand	PFERD
Manufacturer Part Number	4007220930496
Form	Cone with rounded end
Head diameter x cutting edge length	12 x 30 mm
Cutting edge length	30 mm
Length	70 mm
Serration type	INOX
Gross Weight	0.041 kg
Product Group	6AB

EAN

4007220930496