




Dimensions



Model Number

IQC33-20 50pcs

Data carrier

Features

- Operating frequency 13.56 MHz
- Conforms to ISO 15693
- 64 bit Fixcode
- 2000 bytes memory available
- Unlimited writeable
- Degree of protection IP68
- Readable and writable from both sides

Technical data

General specifications

Operating frequency	13.56 MHz
Transfer rate	26 kBit/s

Memory

Chip Type	FRAM MB89R118 (Fujitsu)
Type/Size	FRAM 16 kBit , 8 bytes/block configuration, fixcode 64 Bit
Read cycles	unlimited
Write cycles	unlimited
Data retention period	10 years

Ambient conditions

Ambient temperature	-40 ... 85 °C (-40 ... 185 °F)
Storage temperature	-40 ... 85 °C (-40 ... 185 °F) 160 °C for 50 hours 220 °C for 30 minutes

Mechanical specifications

Degree of protection	IP68
Material	
Housing	PA 6
Mass	1.2 g
Note	Packaging unit, 50-piece

Compliance with standards and directives

Standard conformity	
Degree of protection	EN 60529
RFID	ISO/IEC 15693-1:2010 , ISO/IEC 15693-2:2006 , ISO/IEC 15693-3:2009 , ISO/IEC 18000-3


Notes

The transponder can be read and written from either side.

Read/write distances

- ① IQH1-18GM-V1 ② IQH1-F61-V1 ③ IQH1-FP-V1
- ④ IQH1-F15-V1

Reading range in air IQC33-20



Release date: 2016-04-12 16:24 Date of issue: 2016-04-28 288644_eng.xml