




User's Manual


Features of product ---

- Aluminum Frame, Aluminum cover
- Interface: Support SATA - I, SATA - II
- High performance transfer rate up to 150MB/s, 300MB/s
- Plug & play, hot swappable
- Point to point, free from master/slave setting
- SATA 15Pin & 4Pin Power connectors
- Front Fan x 1, Dust resistant door
- 2 LED for Power & HDD access
- Power Control & Keylock design
- Magic Handle—Auto In/Out
- Color for choice: black or beige
- Dim: 188(L) X 146(W) X 42(H) mm




◆ Magic Handle—Auto In/Out (see picture C)

1. Power LED: Power on, LED indicates Green. (see picture D)
2. Amber LED blinking while HDD access.



Picture C




Picture D


keylock

OPEN


LOCK



◆ Back View & Access LED wiring (Picture E & F)



Picture E



Picture F

1. 15pin Serial ATA Power connector (Pic.E-1)

If your power is from SATA 15pin connector, connect it to the 15pin connector

2. 7pin Serial ATA Signal connector (Pic.E-2)

3. 4pin Power connector (Pic.E-3)

If your power is not from SATA 15pin connector, then, use the 4pin power connector; the 4pin power will automatically be converted to SATA power.

4. HD LED SWITCH (See Pic.E-4)

(The default setting is on the left, supporting SATA-II HD LED)

When the Switch is adjusted to the left, the setting supports SATA-II HD LED;
When the Switch is adjusted to the right, the setting supports SATA-I HD LED, but requiring external HD Access LED wiring (See Picture F).

5. External HDD Access pin connections--

HDD access connection (Note: "+" and "-" position). See it from motherboard manual.

How to connect (See Picture F)

Connect to pins on the motherboard (wire white color is "-"), (see picture F-A)

HD LED (to the computer LED), (see picture F-B)

Connect to HDD pins on the mobile rack (see picture F-C, picture E -5).